


Product	Devices for installation for electronic systems (HBES)
Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Factory	Lexel Fabrika SIA Krustpils 35a LV-1073 Riga Latvia
Ratings	230 V~ 50 Hz 5-200 W or 7-200 W
Trade mark	
Model / Type Ref.	NH3514
Principal characteristics	Universal rotary dimmer LED Local control by rotary knob; Remote control by mechanical push-button in parallel operation; No RF-parts / functionality
A sample of the product was tested and found to be in conformity with	INST EN 60669-1:1999;A1;A2 EN 60669-2-1:2004;A1;A12 EN 60669-2-5:2016 EN 50428:2005;A1;A2
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	See page 3
Additional model(s)	(3) See page 2

Date of issue 11-06-2020



Okhyun Jeon
Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway
TEL +47 22 96 03 30 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Additional model(s)

Product	Devices for installation for electronic systems (HBES)
Pos. No	1
Model / Type Ref.	NH3515
Trade mark (if different from page 1)	
Rating	230 V~ 50 Hz 5-200 W or 7-200 W
Principal characteristics	Wiser universal push-button dimmer LED (with Bluetooth Low Energy (BLE) and ZigBee) Local control by rocker; Remote control by mechanical push-button in parallel operation; Contains RF-parts. It consists Bluetooth Low Energy (BLE) or ZigBee (the RF-chip supported both types); Remote control via a mobile App or other BLE devices by using Bluetooth Low Energy (BLE) protocol or ZigBee hub by ZigBee protocol.; The change from BLE to ZigBee could be done by over the air update.; The change from ZigBee to BLE could be done by making a factory reset as described in the user manual.

Product	Devices for installation for electronic systems (HBES)
Pos. No	2
Model / Type Ref.	NH3516
Trade mark (if different from page 1)	
Rating	230 V~ 50 Hz 5-200 W or 7-200 W
Principal characteristics	Wiser universal rotary dimmer LED (with Bluetooth Low Energy (BLE) and ZigBee) Local control by rotary knob; Remote control by mechanical push-button in parallel operation; Contains RF-parts. It consists Bluetooth Low Energy (BLE) or ZigBee (the RF-chip supported both types); Remote control via a mobile App or other BLE devices by using Bluetooth Low Energy (BLE) protocol or ZigBee hub by ZigBee protocol.; The change from BLE to ZigBee could be done by over the air update.; The change from ZigBee to BLE could be done by making a factory reset as described in the user manual.

Date of issue 11-06-2020



Okhyun Jeon
Certification Department

Product	Devices for installation for electronic systems (HBES)
Pos. No	3
Model / Type Ref.	NH3527
Trade mark (if different from page 1)	
Rating	230 V~ 50 Hz 5-200 W or 7-200 W
Principal characteristics	Wiser motion sensor with universal push-button dimmer LED (with Bluetooth Low Energy (BLE) and ZigBee) Local control by proximity and push-button; Remote control by mechanical push-button in parallel operation; Contains RF-parts. It consists Bluetooth Low Energy (BLE) or ZigBee (the RF-chip supported both types); Remote control via a mobile App or other BLE devices by using Bluetooth Low Energy (BLE) protocol or ZigBee hub by ZigBee protocol.; The change from BLE to ZigBee could be done by over the air update.; The change from ZigBee to BLE could be done by making a factory reset as described in the user manual.

Additional information

Light bulb icon		LED icon		Dimmer icon		Switch icon	
5-100 VA	RC	5-150 VA	L	5-150 VA	C		
5-20 VA	RL						
5-200 W	R	5-150 W	R				

Rated load type NH 3514

Light bulb icon		LED icon		Dimmer icon		Switch icon	
7-100 VA	RC	14-150 W	R	14-150 VA	C		
7-20 VA	RL						
14-200 W	R						
14-150 VA	L						

Rated load type NH3515, NH3516 and NH3527

Date of issue 11-06-2020

Okhyun Jeon
Certification Department