

AENOR

CENELEC Certification Agreement Statement of Test Results (STR)

030/ES0129

AENOR states that by request of:

SCHNEIDER ELECTRIC INDUSTRIES SAS

registered office 35, RUE JOSEPH MONIER 92506 RUEIL MALMAISON CEDEX (France)

a sample of the product Residual current operated circuit-breaker without integral overcurrent protection (RCCB's)

has been tested and found to be in conformity with the standards
UNE-EN 61008-1:2013 (EN 61008-1:2012)
UNE-EN 61008-1:2013/A11:2016 (EN 61008-1:2012/A11:2015)
UNE-EN 61008-1:2013/A1:2015 (EN 61008-1:2012/A1:2014)
UNE-EN 61008-1:2013/A2:2015 (EN 61008-1:2012/A2:2014)
UNE-EN 61008-2-1/A11:1999 (EN 61008-2-1:1994/A11:1998)
UNE-EN 61008-2-1:1996 (EN 61008-2-1:1994)

Test report(s) GS166/17, GS167/17, GS168/17, GS169/17, GS170/17, GS171/17,,
GS172/17, GS173/17, GS174/17, GS175/17, GS232/17.

Trade mark Schneider Electric

See annex for more information.

Manufactured at CM BARRANQUET, 57 46133 MELIANA (Valencia - Spain)

Certification scheme This Statement of Test Results is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard.

This Statement of Test Results has been established by a body which participates in the CENELEC Certification Agreement (CCA) of 11th September 1973 as revised on March 29th, 1983 and September 3rd, 2004. Any other body participating in the CCA may recognize this Statement as a basis for granting a national mark of conformity or a national approval as specified in OD 6, List of current decisions of CCA Group, point 2.11.

First issued on 2018-01-10



Rafael GARCÍA MEIRO
Chief Executive Officer

AENOR

CENELEC Certification Agreement Statement of Test Results (STR)

030/ES0129

Annex to Certificate

Trade mark Schneider Electric

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I Δ m	I m	I n c	I Δ c	Type	Additional information
RCCB1PNSC30AC25	2P	25 A	230V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	AC	Fuse 80 A gG (2)
RCCB1PNSC30AC40	2P	40 A	230V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	AC	Fuse 80 A gG (2)
RCCB1PNSC30ASI25	2P	25 A	230V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	A	Fuse 80 A gG (1)
RCCB1PNSC30ASI40	2P	40 A	230V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	A	Fuse 80 A gG (1)
RCCB1PNSC30A25	2P	25 A	230V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	A	Fuse 80 A gG (1)
RCCB1PNSC30A40	2P	40 A	230V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	A	Fuse 80 A gG (1)
RCCB1PNSC300AC25	2P	25 A	230V-	300mA	50 Hz	1500 A	1500 A	10 kA	10 kA	AC	Fuse 80 A gG (2)
RCCB1PNSC300AC40	2P	40 A	230V-	300mA	50 Hz	1500 A	1500 A	10 kA	10 kA	AC	Fuse 80 A gG (2)
RCCB3PNSC30AC25	4P	25 A	400V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	AC	Fuse 80 A gG (2)
RCCB3PNSC30AC40	4P	40 A	400V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	AC	Fuse 80 A gG (2)
RCCB3PNSC30ASI25	4P	25 A	400V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	A	Fuse 80 A gG (1)
RCCB3PNSC30ASI40	4P	40 A	400V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	A	Fuse 80 A gG (1)
RCCB3PNSC30A25	4P	25 A	400V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	A	Fuse 80 A gG (1)
RCCB3PNSC30A40	4P	40 A	400V-	30mA	50 Hz	1500 A	1500 A	10 kA	10 kA	A	Fuse 80 A gG (1)
RCCB3PNSC300AC25	4P	25 A	400V-	300mA	50 Hz	1500 A	1500 A	10 kA	10 kA	AC	Fuse 80 A gG (2)
RCCB3PNSC300AC40	4P	40 A	400V-	300mA	50 Hz	1500 A	1500 A	10 kA	10 kA	AC	Fuse 80 A gG (2)

(1) Ambient temperature: -25/40°C
(2) Ambient temperature: -5/40°C

First issued on 2018-01-10

Original Electronic Certificate

AENOR INTERNACIONAL S.A.U.
Génova, 6. 28004 Madrid. España
Tel. 91 432 60 00.- www.aenor.com