

CENELEC Certification Agreement

Statement of Test Results (STR)

030/ES0121-M1

AENOR, Spanish Association for Standardization and Certification, states that by request of:

SCHNEIDER ELECTRIC INDUSTRIES SAS

registered office	Electropole 38EQI Eybens - 31 Rue Pierre Mendes France 30050 (Grenoble Cedex 9 - Francia)
a sample of the product	Residual current operated circuit-breaker without integral overcurrent protection (RCCB's)
has been tested and found to be in conformity with the standards	UNE-EN 61008-1:2013+A1:2015+A2:2015 (EN 61008-1:2012+A1:2014+A2:2014) UNE-EN 61008-2-1:1996+A11:1999 (EN 61008-2-1:1994+A11:1998)
Test report(s)	From GS173/15 to GS177/15, GS179/15, GS180/15, from GS182/15 to GS187/15, GS82/16 and GS105/16
Trade mark	Schneider Electric Commercial name "RCCB Domae Biconnect" See annex for more information.
Manufactured at	CM BARRANQUET, 57 46133 MELIANA (Valencia - España)
Certification scheme	This Statement of Test Results is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard. This Statement of Test Results has been established by a body which participates in the CENELEC Certification Agreement (CCA) of 11th September 1973 as revised on March 29th, 1983 and September 3rd, 2004. Any other body participating in the CCA may recognize this Statement as a basis for granting a national mark of conformity or a national approval as specified in OD 6, List of current decisions of CCA Group, point 2.11.
First issued on	2016-06-14


AENOR Asociación Española de Normalización y Certificación

Avelino BRITO
Chief Executive Officer

AENOR

Asociación Española de
Normalización y Certificación

Génova, 6. 28004 Madrid. España
Tel. 902 102 201 – www.aenor.es

CENELEC Certification Agreement

Statement of Test Results (STR)

030/ES0121-M1

Annex to Certificate

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	$I_{\Delta m}$	I_m	I_{nc}	$I_{\Delta c}$	Type	Additional information
B-IDD2P1610AC	2P	16 A	240 V-	10 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD2P2510A	2P	25 A	240 V-	10 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD2P25100AC	2P	25 A	240 V-	100 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD2P2530A-A	2P	25 A	240 V-	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	A	(1)
B-IDD2P2530A-B	2P	25 A	240 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD2P2530AC-A	2P	25 A	240 V-	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD2P2530AC-B	2P	25 A	240 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD2P2530ASI	2P	25 A	240 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD2P25300AC-A	2P	25 A	240 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD2P25300AC-B	2P	25 A	240 V-	300 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD2P25300ACS	2P	25 A	240 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD2P40100AC	2P	40 A	240 V-	100 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD2P4030A-A	2P	40 A	240 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD2P4030A-B	2P	40 A	240 V-	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	A	(1)
B-IDD2P4030AC-A	2P	40 A	240 V-	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD2P4030AC-B	2P	40 A	240 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD2P4030ASI	2P	40 A	240 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD2P40300A	2P	40 A	240 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD2P40300AC-A	2P	40 A	240 V-	300 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD2P40300AC-B	2P	40 A	240 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD2P40300ACS	2P	40 A	240 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD2P40300AS	2P	40 A	240 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD2P40500AC	2P	40 A	240 V-	500 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD2P63100AC	2P	63 A	240 V-	100 mA	50 Hz	630 A	630 A	6000 A	6000 A	AC	(2)
B-IDD2P6330A-A	2P	63 A	240 V-	30 mA	50 Hz	630 A	630 A	6000 A	6000 A	A	(1)
B-IDD2P6330A-B	2P	63 A	240 V-	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	A	(1)
B-IDD2P6330AC-A	2P	63 A	240 V-	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)
B-IDD2P6330AC-B	2P	63 A	240 V-	30 mA	50 Hz	630 A	630 A	6000 A	6000 A	AC	(2)
B-IDD2P63300A	2P	63 A	240 V-	300 mA	50 Hz	630 A	630 A	6000 A	6000 A	A	(1)
B-IDD2P63300AC-A	2P	63 A	240 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)

First issued on 2016-06-14

AENOR Asociación Española de Normalización y Certificación

AENOR Asociación Española de Normalización y Certificación

Génova, 6. 28004 Madrid. España
Tel. 902 102 201 – www.aenor.es

CENELEC Certification Agreement

Statement of Test Results (STR)

030/ES0121-M1

Annex to Certificate

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	Δm	I_m	I_{nc}	Δc	Type	Additional information
B-IDD2P63300AC-B	2P	63 A	240 V-	300 mA	50 Hz	630 A	630 A	6000 A	6000 A	AC	(2)
B-IDD2P63300ACS	2P	63 A	240 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)
B-IDD2P63300AS	2P	63 A	240 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	A	(1)
B-IDD4P25100AC	4P	25 A	415 V-	100 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD4P2530A	4P	25 A	415 V-	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	A	(1)
B-IDD4P2530AC-A	4P	25 A	415 V-	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD4P2530AC-B	4P	25 A	415 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD4P25300AC-A	4P	25 A	415 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD4P25300AC-B	4P	25 A	415 V-	300 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD4P25500AC	4P	25 A	415 V-	500 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD4P40100AC-A	4P	40 A	415 V-	100 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD4P40100AC-B	4P	40 A	415 V-	100 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD4P4030A-A	4P	40 A	415 V-	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	A	(1)
B-IDD4P4030A-B	4P	40 A	415 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD4P4030AC-A	4P	40 A	415 V-	30 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD4P4030AC-B	4P	40 A	415 V-	30 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD4P40300A	4P	40 A	415 V-	300 mA	50 Hz	500 A	500 A	6000 A	6000 A	A	(1)
B-IDD4P40300AC-A	4P	40 A	415 V-	300 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD4P40300AC-B	4P	40 A	415 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	AC	(2)
B-IDD4P40300AS	4P	40 A	415 V-	300 mA	50 Hz	500 A	500 A	3000 A	3000 A	A	(1)
B-IDD4P40500AC	4P	40 A	415 V-	500 mA	50 Hz	500 A	500 A	6000 A	6000 A	AC	(2)
B-IDD4P63100AC-A	4P	63 A	415 V-	100 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)
B-IDD4P63100AC-B	4P	63 A	415 V-	100 mA	50 Hz	630 A	630 A	6000 A	6000 A	AC	(2)
B-IDD4P6330A-A	4P	63 A	415 V-	30 mA	50 Hz	630 A	630 A	6000 A	6000 A	A	(1)
B-IDD4P6330A-B	4P	63 A	415 V-	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	A	(1)
B-IDD4P6330AC-A	4P	63 A	415 V-	30 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)
B-IDD4P6330AC-B	4P	63 A	415 V-	30 mA	50 Hz	630 A	630 A	6000 A	6000 A	AC	(2)
B-IDD4P63300A	4P	63 A	415 V-	300 mA	50 Hz	630 A	630 A	6000 A	6000 A	A	(1)
B-IDD4P63300AC-A	4P	63 A	415 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)
B-IDD4P63300AC-B	4P	63 A	415 V-	300 mA	50 Hz	630 A	630 A	6000 A	6000 A	AC	(2)

First issued on 2016-06-14

AENOR Asociación Española de Normalización y Certificación

AENOR Asociación Española de Normalización y Certificación

Génova, 6. 28004 Madrid. España
Tel. 902 102 201 - www.aenor.es

CENELEC Certification Agreement

Statement of Test Results (STR)

030/ES0121-M1

Annex to Certificate

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	$I_{\Delta m}$	I_m	I_{nc}	$I_{\Delta c}$	Type	Additional information
B-IDD4P63300ACS	4P	63 A	415 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	AC	(2)
B-IDD4P63300AS	4P	63 A	415 V-	300 mA	50 Hz	630 A	630 A	3000 A	3000 A	A	(1)

Additional information

(1) -25°C to 40°C

(2) -5° C to 40°C

AENOR Asociación Española de
Normalización y Certificación

First issued on 2016-06-14