

AENOR

CENELEC Certification Agreement Statement of Test Results (STR)

030/ES0132

AENOR states that by request of:

SCHNEIDER ELECTRIC INDUSTRIES SAS

registered office 35, RUE JOSEPH MONIER - 92506 RUEIL MALMAISON CEDEX (Francia)

a sample of the product Residual current operated circuit-breaker without integral overcurrent protection (RCCB's)

has been tested and found to be in conformity with the standards
UNE-EN 61008-1:2013 (EN 61008-1:2012)
UNE-EN 61008-1:2013/A11:2016 (EN 61008-1:2012/A11:2015)
UNE-EN 61008-1:2013/A1:2015 (EN 61008-1:2012/A1:2014)
UNE-EN 61008-1:2013/A12:2017 (EN 61008-1:2012/A12:2017)
UNE-EN 61008-1:2013/A2:2015 (EN 61008-1:2012/A2:2014)
UNE-EN 61008-2-1/A11:1999 (EN 61008-2-1:1994/A11:1998)
UNE-EN 61008-2-1:1996 (EN 61008-2-1:1994)

Test report(s) GS72/14-M1, GS133/14, GS77/14, GS244/17

Trade mark Schneider Electric
Commercial name "RCCB Helios"
See annex for more information.

Manufactured at CM BARRANQUET, 57 - 46133 MELIANA (Valencia - España)

Certification scheme This Statement of Test Results is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard.

This Statement of Test Results has been established by a body which participates in the CENELEC Certification Agreement (CCA) of 11th September 1973 as revised on March 29th, 1983 and September 3rd, 2004. Any other body participating in the CCA may recognize this Statement as a basis for granting a national mark of conformity or a national approval as specified in OD 6, List of current decisions of CCA Group, point 2.11.

First issued on 2018-05-04



Rafael GARCÍA MEIRO
Chief Executive Officer

AENOR

CENELEC Certification Agreement Statement of Test Results (STR)

030/ES0132

Annex to Certificate

Trade mark Schneider Electric

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I Δ m	I m	I n c	I Δ c	Type	Additional information
IDH2P2530A	2P	25 A	230/240 V-	30 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	A	(1) (3) (4)
IDH2P2530AC	2P	25 A	230/240 V-	30 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	AC	(1) (2) (4)
IDH2P2530ASI	2P	25 A	230/240 V-	30 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	A-Si	(1) (3) (4) (5)
IDH2P25300A	2P	25 A	230/240 V-	300 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	A	(1) (3) (4)
IDH2P25300AC	2P	25 A	230/240 V-	300 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	AC	(1) (2) (4)
IDH2P4030A	2P	40 A	230/240 V-	30 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	A	(1) (3) (4)
IDH2P4030AC	2P	40 A	230/240 V-	30 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	AC	(1) (2) (4)
IDH2P4030ASI	2P	40 A	230/240 V-	30 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	A-Si	(1) (3) (4) (5)
IDH2P4030ASIE	2P	40 A	230/240 V-	30 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	A	(1) (3) (4)
IDH2P40300A	2P	40 A	230/240 V-	300 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	A-Si	(1) (3) (4)
IDH2P40300AC	2P	40 A	230/240 V-	300 mA	50 Hz	1000 A	1000 A	6000 A	6000 A	AC	(1) (2) (4)
IDH2P40300SASI	2P	40 A	230/240 V-	300 mA	50 Hz	630 A	630 A	6000 A	6000 A	A-Si	(1) (3) (4) (5)
IDH2P40300SASIE	2P	40 A	230/240 V-	300 mA	50 Hz	630 A	630 A	6000 A	6000 A	AC	(1) (3) (4)

- (1) Contact Rivets : Mobile Contact (AgSnO₂) ; Fixed Contact (AgC), Mobile Contact Arm (Copper); Fixed Contact Arm (Copper). Output Terminal current carrying Part (Copper)
- (2) -5/40°C. Shall be back up protected by gG 80A fuse.
- (3) -25/40°C. Shall be back up protected by gG 80A fuse.
- (4) Earth leakage current detection chain, with two optional tripping relays
- (5) Digital Type Reference belonging to the special design type "Superimmunised" (SI)

First issued on 2018-05-04

Original Electronic Certificate

AENOR INTERNACIONAL S.A.U.
Génova, 6. 28004 Madrid. España
Tel. 91 432 60 00.- www.aenor.com