

iq.ul.com

Surge Protective Devices
guide info

E314042

Schneider Electric USA, Inc.

Schneider Electric, SURGE PROTECTION BUSINESS, 1751 S 4800 W, Salt Lake City UT 84104

SSP01EMAxxy(d)*

Permanently Connected

<u>SPD Type</u>	<u>Volts (V)</u>	<u>AC/DC DC PV</u>	<u>Phase</u>	<u>Amps (A)</u>	<u>Ambient Min(°C)</u>	<u>Ambient Max(°C)</u>	<u>Mode</u>	<u>VPR (Vpk)</u>	<u>MCOV (V)</u>	<u>In (kA)</u>	<u>SCCR (kA)</u>
1	240/120	AC	1S	n/a	-35	85	L-L	1200	300	20	200
							L-N	900	150		
							L-G	900	150		
							N-G	700	150		

Evaluated to: UL 1449 4th Ed. Rev: 2017-07-21

(d) - Where xx can be 10, 12, 16, 18, 20 (except for model SSP09EMAxxy) or 24 (except for model SSP09EMAxxy) and yy can be D, DF or F.

* - Complementary Listed EMI Filters (FOKY), E314042.

SPDs investigated for Type 1 applications are automatically suitable for Type 2 applications and may be marked for SPD Type 1 and/or Type 2 applications. SPDs only marked "SPD Type 2" are not suitable for Type 1 applications.

Where a minimum ambient temperature is not specified, assume 0°C unless the product is marked otherwise or with an Outdoor use Environmental Rating. See Electrical Equipment for Use in Ordinary Locations (AALZ) for details regarding Environmental Ratings.

Report Date: 2015-04-30

Last Revised: 2017-10-24

© 2017 UL LLC

