

iq.ul.com

Surge Protective Devices
guide info

E314042

Schneider Electric USA, Inc.

Schneider Electric, SURGE PROTECTION BUSINESS, 1751 S 4800 W, Salt Lake City UT 84104

QO250PSPD, QO250PSPDC, CQO250PSPD

Molded Case SPD

<u>SPD Type</u>	<u>Volts (V)</u>	<u>AC/DC DC PV</u>	<u>Phase</u>	<u>Amps (A)</u>	<u>Ambient Min(°C)</u>	<u>Ambient Max(°C)</u>	<u>Mode</u>	<u>VPR (Vpk)</u>	<u>MCOV (V)</u>	<u>In (kA)</u>	<u>SCCR (kA)</u>
1	240/120	AC	1S	n/a	-20	65	L-L L-N	900 500	300 150	20	22

Evaluated to: UL 1449 4th Ed. Rev: 2017-07-21 and CSA C22.2 No. 269.1-14, 2014-14

SPDs investigated for Type 1 applications are automatically suitable for Type 2 applications and may be marked for SPD Type 1 and/or Type 2 applications. SPDs only marked "SPD Type 2" are not suitable for Type 1 applications.

Where a minimum ambient temperature is not specified, assume 0°C unless the product is marked otherwise or with an Outdoor use Environmental Rating. See Electrical Equipment for Use in Ordinary Locations (AALZ) for details regarding Environmental Ratings.

Report Date: 2016-11-22
Last Revised: 2017-10-23

© 2017 UL LLC

