

iq.ul.com

Surge Protective Devices  
guide info

E314042

**Schneider Electric USA, Inc.**

Schneider Electric, SURGE PROTECTION BUSINESS, 1751 S 4800 W, Salt Lake City UT 84104

**SSP06EMAxxy(e)\***

Permanently Connected

| <u>SPD Type</u> | <u>Volts (V)</u> | <u>AC/DC DC PV</u> | <u>Phase</u> | <u>Amps (A)</u> | <u>Ambient Min(°C)</u> | <u>Ambient Max(°C)</u> | <u>Mode</u> | <u>VPR (Vpk)</u> | <u>MCOV (V)</u> | <u>In (kA)</u> | <u>SCCR (kA)</u> |
|-----------------|------------------|--------------------|--------------|-----------------|------------------------|------------------------|-------------|------------------|-----------------|----------------|------------------|
| 2               | 240              | AC                 | 3D           | n/a             | -35                    | 85                     | L-L<br>L-G  | 2000<br>1500     | 300<br>320      | 20             | 200              |

Evaluated to: UL 1449 4th Ed. Rev: 2017-07-21 and CSA Electrical Certification Notice 516/CSA C22.2 No. 8 13

(e) - Where xx can be 32, 36, 40 or 48 and yy can be D, DF, F or blank

\* - Complementary Listed EMI Filters (FOKY), E314042.

SPDs investigated for Type 1 applications are automatically suitable for Type 2 applications and may be marked for SPD Type 1 and/or Type 2 applications. SPDs only marked "SPD Type 2" are not suitable for Type 1 applications.

Where a minimum ambient temperature is not specified, assume 0°C unless the product is marked otherwise or with an Outdoor use Environmental Rating. See Electrical Equipment for Use in Ordinary Locations (AALZ) for details regarding Environmental Ratings.

Report Date: 2015-04-30

Last Revised: 2017-10-24

© 2017 UL LLC

