

iq.ul.com

Surge Protective Devices  
guide info

E314042

**Schneider Electric USA, Inc.**

Schneider Electric, SURGE PROTECTION BUSINESS, 1751 S 4800 W, Salt Lake City UT 84104

**SDSA4040**

Permanently Connected

<u>SPD Type</u>	<u>Volts (V)</u>	<u>AC/DC DC PV</u>	<u>Phase</u>	<u>Amps (A)</u>	<u>Ambient Min(°C)</u>	<u>Ambient Max(°C)</u>	<u>Mode</u>	<u>VPR (Vpk)</u>	<u>MCOV (V)</u>	<u>In (kA)</u>	<u>SCCR (kA)</u>
1	480/277	AC	3Y	n/a	-35	80	L-L	2500	840	10	200
							L-N	1500	420		
1	415/240	AC	3Y	n/a	-35	80	L-L	2500	840	10	200
							L-N	1500	420		
1	400/230	AC	3Y	n/a	-35	80	L-L	2500	840	10	200
							L-N	1500	420		
1	380/220	AC	3Y	n/a	-35	80	L-L	2500	840	10	200
							L-N	1500	420		

Evaluated to: UL 1449 4th Ed. Rev: 2017-07-21 and CSA Electrical Certification Notice 516/CSA C22.2 No. 8 13

SPDs investigated for Type 1 applications are automatically suitable for Type 2 applications and may be marked for SPD Type 1 and/or Type 2 applications. SPDs only marked "SPD Type 2" are not suitable for Type 1 applications.

Where a minimum ambient temperature is not specified, assume 0°C unless the product is marked otherwise or with an Outdoor use Environmental Rating. See Electrical Equipment for Use in Ordinary Locations (AALZ) for details regarding Environmental Ratings.

Report Date: 2015-05-01  
Last Revised: 2017-10-23

© 2017 UL LLC

