

Schneider Electric USA, Inc.

Schneider Electric, SURGE PROTECTION BUSINESS, 1751 S 4800 W, Salt Lake City UT 84104

TVS91MAxx (b)

Permanently Connected

<u>SPD Type</u>	<u>Volts (V)</u>	<u>AC/DC DC PV</u>	<u>Phase</u>	<u>Amps (A)</u>	<u>Ambient Min(°C)</u>	<u>Ambient Max(°C)</u>	<u>Mode</u>	<u>VPR (Vpk)</u>	<u>MLV (Vpk)</u>	<u>MCOV (V)</u>	<u>Vn (Vdc)</u>	<u>In (kA)</u>	<u>SCCR (kA)</u>	<u>Notes</u>
2CA (4-2)	600	AC	3D	N/A	-35	85	L-L	2500	-	700	-	10	200	1
							L-G	2500	-	700	-	-	-	-
2CA (4-2)	480/277	AC	3Y	N/A	-35	85	L-L	2500	-	700	-	10	200	1
							L-G	2500	-	700	-	-	-	-
2CA (4-2)	380/220	AC	3Y	N/A	-35	85	L-L	2500	-	700	-	10	200	1
							L-G	2500	-	700	-	-	-	-
2CA (4-2)	400/230	AC	3Y	N/A	-35	85	L-L	2500	-	700	-	10	200	1
							L-G	2500	-	700	-	-	-	-
2CA (4-2)	415/240	AC	3Y	N/A	-35	85	L-L	2500	-	700	-	10	200	1
							L-G	2500	-	700	-	-	-	-

Evaluated to: UL 1449 4th Ed. Rev: 2017-07-21 and CSA Electrical Certification Notice 516/CSA C22.2 No. 8 13

(b) - Where xx can be 10, 12, 16, 18, 20, 24, 30, 32, 36, or 48. Also complimentary Recognized as an EMI filter.

Note 1 - Suitable for Factory wiring only.

SPDs investigated for Type 1 applications are automatically suitable for Type 2 applications and may be marked for SPD Type 1 and/or Type 2 applications. SPDs only marked "SPD Type 2" are not suitable for Type 1 applications.

Where a minimum ambient temperature is not specified, assume 0°C unless the product is marked otherwise or with an Outdoor use Environmental Rating. See Electrical Equipment for Use in Ordinary Locations (AALZ) for details regarding Environmental Ratings.

Report Date: 2009-11-10

Last Revised: 2017-10-23

© 2017 UL LLC

