


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product	Circuit-breakers for overcurrent protection for household and similar installations
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the manufacturer	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 MERLIN GERIN ALÈS 16 Boulevard Charles Peguy, 30319 Alès Cedex France
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	1P+N – Ue = 230 V – 50-60 Hz – Icn = 4500 A In = 6, 10, 13, 16, 20, 25, 32 or 40 A (curve B circuit-breakers) In = 2, 4, 6, 10, 13, 16, 20, 25, 32 or 40 A (curve C circuit-breakers) (see Additional Sheet and page 6 of Test Report No. PB16-0009380-09-00)
Trademark (if any)	 Schneider Electric
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Series iDPN40 (see Additional Sheet and page 8 of Test Report No. PB16-0009380-09-00)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2 This CB Test Certificate supersedes the CBTC No. IT-18962 dated 2018-05-11. Modification introduced: new factory address.
A sample of the product was tested and found to be in conformity with	IEC 60898-1:2015
As shown in the Test Report Ref. No. which forms part of this Certificate	PB16-0009380-09-00, from PB16-0009380-09-01 to PB16-0009380-09-18 and PB19-0045933-01-02

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.  
Via Quintiliano 43, IT-I-20138 Milano, Italy

**Description of the circuit-breakers for overcurrent protection series iDPN40 ( $I_{cn} = 4500 \text{ A}$ )**

Curve	Rated current	Generic reference
B	6 A	MCB1PNSC456B6
	10 A	MCB1PNSC456B10
	13 A	MCB1PNSC456B13
	16 A	MCB1PNSC456B16
	20 A	MCB1PNSC456B20
	25 A	MCB1PNSC456B25
	32 A	MCB1PNSC456B32
	40 A	MCB1PNSC456B40
C	2 A	MCB1PNSC456C2 or MCB1PNSC4545C2
	4 A	MCB1PNSC456C4
	6 A	MCB1PNSC456C6 or MCB1PNSC4545C6
	10 A	MCB1PNSC456C10 or MCB1PNSC4545C10
	13 A	MCB1PNSC456C13
	16 A	MCB1PNSC456C16 or MCB1PNSC4545C16
	20 A	MCB1PNSC456C20 or MCB1PNSC4545C20
	25 A	MCB1PNSC456C25 or MCB1PNSC4545C25
	32 A	MCB1PNSC456C32 or MCB1PNSC4545C32
	40 A	MCB1PNSC456C40 or MCB1PNSC4545C40