

CERTIFICATE

Issued to:
Applicant:
Schneider Electric Industries SAS
Electropole 38EQI
31 rue Pierre Mendes
38050 Grenoble Cedex 9, France

Manufacturer/Licensee:
Schneider Electric Industries SAS
Electropole 38EQI
31 rue Pierre Mendes
38050 Grenoble Cedex 9, France

Products : Surge protective devices
Trade name : SCHNEIDER ELECTRIC
Types/models : iQuick PRD 8r ...
iQuick PRD 20r ...

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 61643-11:2012; IEC 61643-11:2011;
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 2115383

DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.


This certificate is issued on: 24 June 2014 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 2170494.01

DEKRA Certification B.V.



drs. G.J. Zoetbrood
Managing Director



H.R.M. Barends
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Products	:	Surge protective devices
Trade name	:	SCHNEIDER ELECTRIC
Types	:	iQuick PRD 8r 2P iQuick PRD 8r 3P iQuick PRD 8r 4P iQuick PRD 20r 2P iQuick PRD 20r 3P iQuick PRD 20r 4P iQuickPRD Cartridge C 8-350 iQuickPRD Cartridge C 20-350 iQuickPRD Cartridge C Neutral-350
SPD type (and test class)	:	Type 2 (II)
Short-circuit current rating (I_{scrr})	:	25 kA

Product data - type iQuick PRD 8r 2P

Commercial reference	:	A9L16298
Number of poles	:	2-pole
Maximum continuous operating voltage (U_c)	:	L/N: 350 Vac N/PE: 264 Vac
Nominal discharge current (I_n)	:	2 kA
Maximum discharge current (I_{max})	:	8 kA
Voltage protection level (U_p)	:	L/N: 1,2 kV N/PE 1,7 kV

Product data - type iQuick PRD 8r 3P

Commercial reference	:	A9L16299
Number of poles	:	3-pole
Maximum continuous operating voltage (U_c)	:	L/PEN: 350 Vac
Nominal discharge current (I_n)	:	2 kA
Maximum discharge current (I_{max})	:	8 kA
Voltage protection level (U_p)	:	L/PEN: 1,2 kV

Product data - type iQuick PRD 8r 4P

Commercial reference	:	A9L16300
Number of poles	:	4-pole
Maximum continuous operating voltage (U_c)	:	L/N: 350 Vac N/PE: 264 Vac
Nominal discharge current (I_n)	:	2 kA
Maximum discharge current (I_{max})	:	8 kA
Voltage protection level (U_p)	:	L/N: 1,2 kV N/PE: 1,7 kV

Product data - type iQuick PRD 20r 2P

Commercial reference	:	A9L16295
Number of poles	:	2-pole
Maximum continuous operating voltage (U_c)	:	L/N: 350 Vac N/PE: 264 Vac
Nominal discharge current (I_n)	:	5 kA
Maximum discharge current (I_{max})	:	20 kA
Voltage protection level (U_p)	:	L/N: 1,5 kV N/PE 1,7 kV

Product data - type iQuick PRD 20r 3P

Commercial reference	:	A9L16296
Number of poles	:	3-pole
Maximum continuous operating voltage (U_c)	:	L/PEN: 350 Vac
Nominal discharge current (I_n)	:	5 kA
Maximum discharge current (I_{max})	:	20 kA
Voltage protection level (U_p)	:	L/PEN: 1,5 kV

Product data - type iQuick PRD 20r 4P

Commercial reference	:	A9L16297
Number of poles	:	4-pole
Maximum continuous operating voltage (U_c)	:	L/N: 350 Vac N/PE: 264 Vac
Nominal discharge current (I_n)	:	5 kA
Maximum discharge current (I_{max})	:	20 kA
Voltage protection level (U_p)	:	L/N: 1,5 kV N/PE: 1,7 kV

Product data - type iQuickPRD Cartridge C 20-350

Commercial reference	:	A9L16311
Cartridge	:	for iQuick PRD 20r for L-(PE)N protection

Product data - type iQuickPRD Cartridge C 8-350

Commercial reference	:	A9L16312
Cartridge	:	for iQuick PRD 8r for L-(PE)N protection

Product data - type iQuickPRD Cartridge C Neutral-350

Commercial reference	:	A9L16313
Cartridge	:	for iQuick PRD ... for N-PE protection

TESTS**Test requirements**

EN 61643-11:2012

IEC 61643-11:2011

Test result

The test results are laid down in DEKRA test file 2170494.01.

Remarks

This certificate replaces certificate 2158002.01 issued on 1 November 2012.

Conclusion

The examination proved that all test requirements were met.

Tested by : C.H.J. Addink

Checked by : C.C. Burger

Two handwritten signatures in blue ink. The first signature is above the 'Tested by' line, and the second is above the 'Checked by' line.**Factory locations**

Schneider Electric Hungaria, Villamossagi Zrt.

Hock János út. 55, 8900, Zalaegerszeg

Hungary