


**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product	Circuit-breakers for overcurrent protection for household and similar installations
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the manufacturer	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 SCHNEIDER ELECTRIC HUNGÁRIA VILLAMOSSÁGI ZRT. Hock János utca 55 8900 Zalaegerszeg Hungary
Ratings and principal characteristics	3P+N – U <sub>e</sub> = 400 V – 50-60 Hz – I <sub>cn</sub> = 6000 A I <sub>n</sub> = 6, 10, 13, 16, 20, 25, 32 or 40 A (curve B and curve C circuit-breakers) I <sub>n</sub> = 6, 10, 13, 16, 20, or 25 A (curve D circuit-breakers) (see Additional Sheet and page 6 of Test Report No. PB16-0009380-15-00)
Trademark (if any)	 Schneider Electric
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Series iQPN40 (see Additional Sheet and page 8 of Test Report No. PB16-0009380-15-00)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60898-1:2015
As shown in the Test Report Ref. No. which forms part of this Certificate	PB16-0009380-15-00 and from PB16-0009380-15-01 to PB16-0009380-15-22

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.  
Via Quintiliano 43, IT-I-20138 Milano, Italy



**Description of the circuit-breakers for overcurrent protection series iQPN40 ( $I_{cn} = 6000 \text{ A}$ )**

Curve	Rated current	Generic reference
B	6 A	MCB3PNSC610B6
	10 A	MCB3PNSC610B10
	13 A	MCB3PNSC610B13
	16 A	MCB3PNSC610B16
	20 A	MCB3PNSC610B20
	25 A	MCB3PNSC610B25
	32 A	MCB3PNSC610B32
	40 A	MCB3PNSC610B40
C	6 A	MCB3PNSC610C6
	10 A	MCB3PNSC610C10
	13 A	MCB3PNSC610C13
	16 A	MCB3PNSC610C16
	20 A	MCB3PNSC610C20
	25 A	MCB3PNSC610C25
	32 A	MCB3PNSC610C32
	40 A	MCB3PNSC610C40
D	6 A	MCB3PNSC610D6
	10 A	MCB3PNSC610D10
	13 A	MCB3PNSC610D13
	16 A	MCB3PNSC610D16
	20 A	MCB3PNSC610D20
	25 A	MCB3PNSC610D25