



FIELD WIRING TIGHTENING TORQUES &
INSTRUCTIONS FOR M.C.C. TERMINAL BLOCKS

10A CONTROL WIRE TERMINAL BLOCK




TO SEPARATE OR REMOVE THE TOP PORTION OF THE TERMINAL BLOCK FROM THE BASE, GRASP THE TOP HALF AND PULL APART AS SHOWN. EACH TERMINAL IS RATED FOR ONE 16-12 AWG WIRE OR TWO 16 AWG WIRES. TORQUE TERMINAL SCREWS TO 5 IN-LBS.

25A CONTROL WIRE TERMINAL BLOCK



TO SEPARATE OR REMOVE THE TOP PORTION OF THE TERMINAL BLOCK FROM THE BASE, GRASP THE TOP HALF AND PULL APART AS SHOWN. EACH TERMINAL IS RATED FOR ONE 16-12 AWG WIRE OR TWO 16-14 AWG WIRES. TORQUE TERMINAL SCREWS TO 7-10 IN-LBS.

175A POWER WIRE TERMINAL BLOCK



TORQUE WIRE TERMINALS TO THE FOLLOWING VALUES PER WIRE SIZE:

14-10 AWG	35 IN-LBS.
8 AWG	40 IN-LBS.
6-2/0 AWG	120 IN-LBS.

FOR COPPER WIRE ONLY SIZED PER 60°C OR 75°C NEC WIRE RATINGS

SQUARE D COMPANY