

# Combination AC Disconnect/ GFI Receptacle

Additional code requirements don't have to mean additional cost



**The Square D® Combination AC Disconnect and GFI Receptacle unit will help you save time and material when wiring to NEC 210.63 requirements. This all-in-one unit provides the air-conditioning disconnect and GFI receptacle in one NEMA 3R enclosure, eliminating the need for a separate box and weatherproof receptacle cover.**

- 20A GFI Receptacle mounted to trim for easy wiring (requires separate 120V circuit)
- Non-fused 60A pullout
- Side-opening door offers maximum accessibility and when shut, provides a weatherproof cover for the receptacle per the requirements of NEC 406.8
- Convenient combination knockout provisions (1/2", 3/4", 1") on side, back and bottom enclosure walls for maximum wiring flexibility
- Mounting slot for pre-hanging during installation
- Receptacle factory-wired to ground
- Swing down cover padlock provision
- Pull-out head storage in OFF position
- Also available with 20A non-GFI receptacle

## Not Fusible Combination Air Conditioning Disconnect/Receptacle Units Rainproof – UL Listed (Single Phase, 2 Wire – 240 Vac Maximum)

Ampere Rating	Catalog Number*	Description	Max. Hp	Wire Range Al/Cu		Dimensions			Package Weight	Individual Pkg UPC Code
				Line/Load	Equipment Grounding Terminals	D"	W"	H"		
60	UFP222RGFI	Not-Fusible Pullout and 20A GFI Duplex Receptacle	10	#14-#3	(3) #14-#4	5.40	5.25	7.40	4.25 lbs.	7-85901-60710-6
60	UFP222RD	Not-Fusible Pullout and 20A Duplex Receptacle	10	#14-#3	(3) #14-#4	5.40	5.25	7.40	4.25 lbs.	7-85901-42026-2

\*Does not contain overcurrent protection. Suitable for use on a system with 10,000 RMS symmetrical amperes available fault current at 240 Vac maximum when protected by a fuse or circuit breaker rated 60A or less.

