Ultrasonic Sensor M30 - Straight or 90° angled version

Plastic XXA30P1•M12 Ni-plated Brass: XX•30B1•M12

Stainless steel ..: XX•30S1•M12





▲ WARNING


UNINTENDED EQUIPMENT OPERATION

Do not use this product to detect objects within the deadband (blind zone) or outside the sensing window.

Failure to follow these instructions can result in death, serious injury, or equipment damage.

http://qr.tesensors.com/XX0003

Dimensions XXA30B1•M12 XXA30S1•M12







BN

WH


BU



Connectors wiring




Pin Number	Wire Color	Description	
1	BN: Brown	+1224 Vdc	
2	WH: White	Input teach	
3	BU: Blue	0 Vdc	
4	BK: Black	Output	
(5)	GY: Grey	Synchronization	




Note: (1): See synchronization section


Note: (1): See synchronization section


















4–20 mA:
- For 12 Vdc, Load ≤ 250 Ω
- For 24 Vdc, Load ≤ 850 Ω

Synchronization (side by side application)



Synchronization operation


Up to 8 sensors can be synchronized to operate side by side by electrically connecting all pin no.5 (grey) wires together. To synchronize one than 8 sensors a PLC output can be used (the pins no.5 must be simultaneously driven by the rising edge of a pulse).

NOTE (1): The pulse must be at a high level of 12 to 24 Vdc and a low level of 0 to 2Vdc. All sensors should be the same model and have the same cycle time setting. The high pulse width should be 1 ms, and the low should be at be at least as long as the sensor cycle time setting (Sn = 1 m: default cycle time = 15 ms).

NOTE (2): When the pin no.5 is at low level or at high level, object sensing is suspended and the sensor output holds the last valid output citch before supposition.

state before suspension.


Multiplexing (face to face application)



This function can be used to avoid disturbances when operating sensors face to face. A unique address must be assigned to each sensor (or group of sensors) with the use of the XX Configuration Software (prior to wiring the sensors), and all pin no.5 (grey) wires must be connected together For sequencing with a PLC, please contact your local Telemecanique Sensors Technical Support Group.

Electrical equipment should be installed, operated, serviced, and maintained only by qualified personnel. No responsibility is assumed by Schneider Electric for any consequences arising out of the use of this material.

© 2019 Schneider Electric. "All Rights Reserved."



Detection curves for different objects

Detection curve with 100 x 100 mm square target



(*): Blind zone

100 x 100 mm / 3.94 x 3.94 in. Stainless steel plate



Detection curve with round bar



Ø 10 mm / 0.394 in. Stainless steel cylinder


Ø 25 mm / 0.984 in. Stainless steel cylinder




Wiring accessory



Mounting accessory



Recommended to use for sensor applications at operating temperatures -25 ... 0 $^{\circ}$ C (-13...32 $^{\circ}$ F)



Cables

5-pin, 5-wire (for synchronization)



XZCPV11V12L2 (2 m / 6.6 ft) XZCPV11V12L5 (5 m / 16.4 ft) XZCPV11V12L10 (10 m / 32.8 ft)

XZCPV12V12L2 (2 m / 6.6 ft) XZCPV12V12L5 (5 m / 16.4 ft) XZCPV12V12L10 (10 m / 32.8 ft)


5-pin, 4-wire (no synchronization)


XZCP1141L2 (2 m / 6.6 ft) XZCP1141L5 (5 m / 16.4 ft) XZCP1141L10 (10 m / 32.8 ft) XZCP1241L2 (2 m / 6.6 ft) XZCP1241L5 (5 m / 16.4 ft) XZCP1241L10 (10 m / 32.8 ft)

M12 connectors









Scan the Qr-code to access this Instruction Sheet in different languages.



Note:
You can download this Instruction Sheet in different languages from our website at: www.tesensors.com
We welcome your comments about this document. You can reach us by e-mail at: customer-support@tesensors.com

http://qr.tesensors.com/XX0003