

SCHNEIDER ELECTRIC Advantys STB Modules and Accessories:

STBACI1225	ANALOG C IN 2CH 4-20MA SGL-END 10BIT BSC
STBACI1230	ANALOG C IN 2CH 0-20MA SGL-END 12 BIT
STBACO1210	ANALOG C OUT 2CH 0-20MA SGL-END 12 BIT
STBACO1225	ANALOG C OUT 2CH 4-20MA SGL-END 10BT BSC
STBART0200	ANALOG IN 2CH RTD/TC/MV ISO 16 BIT
STBAVI1255	ANALOG V IN 2CH 0-10V SGL-END 10BIT BSC
STBAVI1270	ANALOG V IN 2CH -/+10V SGL-END 12 BIT
STBAVI1275	ANALOG V IN 2CH -/+10V SGL-END 10BIT BSC
STBAVO1250	ANALOG V OUT 2CH -/+10V SGL-END 12 BIT
STBAVO1255	ANALOG V OUT 2CH 0-10V SGL-END 10BIT BSC
STBAVO1265	ANALOG V OUT 2CH -/+10V SGL-END 10BT BSC
STBDAO8210	115/230VAC OUT 2PT 2A
STBDDI3230	24VDC IN 2PT SINK 4WIRE 0.2MS CFG SCP
STBDDI3420	24VDC IN 4PT SINK 3WIRE 0.5MS CFG SCP
STBDDI3425	24VDC IN 4PT SINK 3WIRE BASIC
STBDDI3610	24VDC IN 6PT SINK 2WIRE 1MS FIXED SCP
STBDDI3615	24VDC IN 6PT SINK 2WIRE BASIC
STBDDO3200	24VDC OUT 2PT SOURCE 0.5A OCP
STBDDO3230	24VDC OUT 2PT SOURCE 2.0A OCP
STBDDO3410	24VDC OUT 4PT SOURCE 0.5A OCP
STBDDO3415	24VDC OUT 4PT SOURCE .25A BASIC
STBDDO3600	24VDC OUT 6PT SOURCE 0.5A OCP
STBDDO3605	24VDC OUT 6PT SOURCE .25A BASIC
STBDRA3290	RELAY OUT 2PT FORM A/B 7A 24V COIL
STBDRC3210	RELAY OUT 2PT FORM C 2A 24V COIL
STBEHC3020	HIGH SPEED CNTR 1CH INC 40KHZ
STBEPI1145	TEGO POWER 16IN/8OUT I/F
STBEPI2145	TESYS TYPE U 12IN/8OUT PREWIRING I/F
STBNCO1010	CANOPEN NIM BASIC
STBNCO2212	CANOPEN NIM STANDARD
STBNDN1010	DEVICENET NIM BASIC
STBNDN2212	DEVICENET NIM STANDARD
STBNDP1010	PROFIBUS DP NIM BASIC
STBNDP2212	PROFIBUS DP NIM STANDARD
STBNFP2212	FIP IO NIM STANDARD
STBNIB1010	INTERBUS NIM BASIC
STBNIB2212	INTERBUS NIM STANDARD
STBNIP2212	ETHERNET MB TCP/IP NIM STANDARD
STBNMP2212	MODBUS PLUS NIM STANDARD

Attachment to Certificate No.17-GE1585769-PDA dated 13 January 2017

STBPDT2100	115/230VAC PDM STANDARD
STBPDT2105	115/230VAC PDM BASIC
STBPDT3100	24VDC PDM STANDARD
STBPDT3105	24VDC PDM BASIC
STBXBA1000	I/O BASE SIZE1
STBXBA2000	I/O BASE SIZE2
STBXBA2200	PDM BASE
STBXBA2300	BOS EXTENSION BASE
STBXBA2400	EOS EXTENSION BASE 18MM
STBXBA3000	I/O BASE SIZE3
STBXBE1000	EOS EXTENSION MODULE
STBXBE1200	BOS EXTENSION MODULE
STBXBE2100	CANOPEN EXTENSION MODULE
STBXCA1001	0.3M ISLAND BUS EXTENSION CABLE
STBXCA1002	1M ISLAND BUS EXTENSION CABLE
STBXCA1003	4.5M ISLAND BUS EXTENSION CABLE
STBXCA1004	10M ISLAND BUS EXTENSION CABLE
STBXCA1006	14M ISLAND BUS EXTENSION CABLE
STBXCA3002	1.0M TEGO POWER CABLE
STBXCA3003	2.0M TEGO POWER CABLE
STBXCA4002	RS232 CONFIG CABLE
STBXMP1100	TERMINATION PLATE - SPARE
STBXMP4440	MEMORY CARD 32K
STBXTS1100	QTY 206PT I/O SCREW CONN KIT
STBXTS1110	QTY 205PT I/O SCREW CONN KIT
STBXTS1111	5PT DEVICENET SCREW CONN
STBACI0320	ANALOG C IN 4CH 4-20MA 16 BIT
STBACI0320K	ANALOG C IN 4CH,4-20MA KIT CONNS,BASE
STBACI0320KC	ANALOG C IN 4CH, 4-20 MA KIT CLAMP, BASE
STBACI0320KS	ANALOG C IN 4CH, 4-20 MA KIT SCREW, BASE
STBACI1225	ANALOG C IN 2CH 4-20MA SGL-END 10BIT BSC
STBACI1225K	ANALOG C IN 2CHBASIC4-20AKIT CONNS,BASE
STBACI1225KC	ANALOG C IN 2CHBASIC4-20MAKIT CLAMP,BASE
STBACI1225KS	ANALOG C IN 2CHBASIC4-20MAKIT SCREW,BASE
STBACI1230K	ANALOG C IN 2CH 0-20MA KIT CONNS,BASE
STBACI1230KC	ANALOG C IN 2CH 0-20MA KIT CLAMP, BASE
STBACI1230KS	ANALOG C IN 2CH 0-20MA KIT SCREW, BASE
STBACI1400	ANALOG C IN 8 CH, 16 BIT SINGLE ENDED
STBACI1400K	ANALOG C IN 8CH KIT CONNS,BASE
STBACI1400KC	ANALOG C IN 8CH KIT CLAMP CONN BASE
STBACI1400KS	ANALOG C IN 8CH KIT SCREW CONN BASE

Attachment to Certificate No.17-GE1585769-PDA dated 13 January 2017

STBACI8320	ANALOG C IN 4CH HART 4-20MA 16 BIT
STBACI8320K	ANALOG C IN 4CH HART KIT CONNS,BASE
STBACI8320KC	ANALOG C IN 4CH HART KIT CLAMP,BASE
STBACI8320KS	ANALOG C IN 4CH HART KIT SCREW, BASE
STBACO0120	ANALOG C OUT 1 CH, 4-20MA 16 BIT
STBACO0120K	ANALOG C OUT 1CH KIT CONNS,BASE
STBACO0120KC	ANALOG C OUT 1CH KIT CLAMP CONN BASE
STBACO0120KS	ANALOG C OUT 1CH KIT SCREW CONN BASE
STBACO0220	ANALOG C OUT 2CH 4-20MA 16 BIT
STBACO0220K	ANALOG C OUT 2CH 16 BIT KIT CONNS, BASE
STBACO0220KC	ANALOG C OUT 2CH 16 BIT KIT CLAMP,BASE
STBACO0220KS	ANALOG C OUT 2CH 16 BIT KIT SCREW,BASE
STBACO1210K	ANALOG C OUT 2CH 0-20MA KIT CONNS,BASE
STBACO1210KC	ANALOG C OUT 2CH 0-20MA KIT CLAMP,BASE
STBACO1210KS	ANALOG C OUT 2CH 0-20MA KIT SCREW,BASE
STBACO1225K	ANALOG C OUT 2CHBASIC4-20 KIT CONNS,BASE
STBACO1225KC	ANALOG C OUT 2CHBASIC4-20 KIT CLAMP,BASE
STBACO1225KS	ANALOG C OUT 2CHBASIC4-20 KIT SCREW,BASE
STBART0200K	ANALOG IN 2CH RTD/TC/MV KIT CONNS,BASE
STBART0200KC	ANALOG IN 2CH RTD/TC/MV KIT CLAMP, BASE
STBART0200KS	ANALOG IN 2CH RTD/TC/MV KIT SCREW, BASE
STBAVI0300	ANALOG V IN 4 CH, VOLT 16 BIT
STBAVI0300K	ANALOG V IN 4CH KIT CONNS,BASE
STBAVI0300KC	ANALOG V IN 4CH KIT CLAMP CONN BASE
STBAVI0300KS	ANALOG V IN 4CH KIT SCREW CONN BASE
STBAVI1255K	ANALOG 0-10V IN 2CH BASE KIT CONNS,BASE
STBAVI1255KC	ANALOG 0-10V IN 2CH BASIC KIT CLAMP, BAS
STBAVI1255KS	ANALOG 0-10V IN 2CH BASIC KIT SCREW, BAS
STBAVI1270K	ANALOG -/+10V IN 2CH KIT
STBAVI1270KC	ANALOG -/+10V IN 2CH KIT CLAMP CONN, BAS
STBAVI1270KS	ANALOG -/+10V IN 2CH KIT SCREW CONN, BAS
STBAVI1275K	ANALOG-/+10V IN 2CH BASE KIT CONNS,BASE
STBAVI1275KC	ANALOG-/+10V IN 2CH BASIC KIT CLAMP, BAS
STBAVI1275KS	ANALOG-/+10V IN 2CH BASIC KIT SCREW, BAS
STBAVI1400	ANALOG V IN 8CH, 16 BIT SINGLE ENDED
STBAVI1400K	ANALOG V IN 8CH KIT CONNS,BASE
STBAVI1400KC	ANALOG V IN 8CH KIT CLAMP CONN BASE
STBAVI1400KS	ANALOG V IN 8CH KIT SCREW CONN BASE
STBAVO0200	ANALOG V OUT 2 CH, VOLT 16 BIT
STBAVO0200K	ANALOG V OUT 2CH KIT CONNS,BASE
STBAVO0200KC	ANALOG V OUT 2CH KIT CLAMP CONN,BASE

Attachment to Certificate No.17-GE1585769-PDA dated 13 January 2017

STBAVO0200KS	ANALOG V OUT 2CH KIT SCREW CONN,BASE
STBAVO1250	ANALOG-/+10V OUT 2CH KIT CONNS,BASE
STBAVO1250K	ANALOG-/+10V OUT 2CH KIT CONNS,BASE
STBAVO1250KC	ANALOG -/+10V OUT 2CH KIT CLAMP, BASE
STBAVO1250KS	ANALOG -/+10V OUT 2CH KIT SCREW, BASE
STBAVO1255K	ANALOG 0-10V OUT 2CHBASIC KIT CONNS,BASE
STBAVO1255KC	ANALOG 0-10V OUT 2CHBASIC KIT CLAMP,BASE
STBAVO1255KS	ANALOG 0-10V OUT 2CHBASIC KIT SCREW,BASE
STBAVO1265K	ANALOG-/+10V OUT 2CHBASIC KIT CONNS,BASE
STBAVO1265KC	ANALOG-/+10V OUT 2CHBASIC KIT CLAMP,BASE
STBAVO1265KS	ANALOG-/+10V OUT 2CHBASIC KIT SCREW,BASE
STBCPS2111	AUXILARY POWER SUPPLY
STBCPS2111K	AUX POWER SUPPLY KIT CONN,BASE
STBCPS2111KC	AUX POWER SUPPLY KIT CLAMP,BASE
STBCPS2111KS	AUX POWER SUPPLY KIT SCREW,BASE
STBDAI5230	115VAC IN 2PT 3WIRE FIXED
STBDAI5230K	115VAC IN 2PT KIT CONNS,
STBDAI5230KC	115VAC IN 2PT KIT CLAMP CONN, BASE
STBDAI5230KS	115VAC IN 2PT KIT SCREW CONN, BASE
STBDAI5260	115VAC IN 2PT ISOLATED FIXED

Attachment to Certificate No.17-GE1585769-PDA dated 13 January 2017

Drwg. No.	Title	Ver.
31002384	24 V DC Power Distribution Terminal	6
31002429	2 Channel AC Out	9
31002441	2 Channel 120/240 V AC Input	8
31002449	2 Channel 120/240 V AC Input	8
31002450	2 Channel 24 V DC Input	6
31002455	2 Channel 24 V DC High Current Output	9
31002465	2 Point 24 VDC Inout Module	7
31002470	2 PT Relay Out	7
31002792	120/240 V AC Power Distribution	6
31005217	DC 24 V DC 4 Channel	0
31005225	4 Channel 24 V DC Output	1
31005229	DC Input, 24 V DC, 6 Point	0
31005231	6 Channel 24 V DC Output	1
31005232	PCB 10 V DC Analog Input Module	2
31005233	Analog Voltage Input, 2 Channel	1
31005350	Schematic Drawing	6
31005363	Analog Voltage Input, 2 Channel	1
31005364	PCB STBACI1225	1
31005365	Analog Current Input, 2 C	0
31005369	2 Channel Analog Current Output	1
31005463	Analog Voltage Output, 2 Channel	1
31005464	Analog Voltage Output, 2 Channel	1
31005502	Analog Voltage Output, 2 Channel	0
31005504	Analog Voltage Output, 2 Channel	0
31005519	2 Channel Analog Current Output	1
31005523	4 Channel 24 V DC Output	1
31005524	6 Channel 24 V DC Output	1
31005526	DC Input, 24 V DC, 6 Point	0
31005528	DC Input, 24 V DC, 6 Point	0
31005535	120/240 V AC PDM Basis	1
31005538	24 V DC PDM Basis	1
31006060	Schematic Drawing	1
31006149	Schematic Drawing	0
31006161	Schematic Drawing	1
31006173	24 VDC 16 PT Output Module	0
31006350	Schematic Drawing	1
31006380	Schematic Drawing	1
31006530	Schematic Drawing	2
31006542	Schematic Drawing	8
31006753	Schematic Drawing	6
31006754	Schematic Drawing	6
31006824	Schematic Drawing	4

Attachment to Certificate No.17-GE1585769-PDA dated 13 January 2017

Drwg. No.	Title	Ver.
31006836	Schematic Drawing	4
31006837	Single Ended Input Module	4
31006958	Schematic Drawing	2
31006960	Schematic Drawing	2
31007784	E30 Schematic	1
31007809	CC Power Supply Ethernet	6
31007816	CC Power Supply Profibus	2
31008104	PBA STB NIC 2212	4
31008120	PBA STB NIC 2212 PS	4
33001550	STB_CM_INTERBUS-S	3
33001551	STB_CC_CAN_DP	2
33001557	STB_CC_INTERBUS	4
33001824	STB_CC_CAN_DEVNET_DP	6
33001830	STB_CC_DEVICENET	6
33002127	STB_CC_FIP	3
3100832603	PBA POWER SUPPLY	2
33002133	STB_MODBUS_PLUS	3
33002189	STB-End of Segment Top	1
33002359	STB_CM_CORI	3
33002434	STB-CAN-EXTENDER TOP	4
33002606	STB_CC_CORI	0
33003600	STB_CC_CAN_DEVNET_DP	1
33003604	SRB_CC_FIP	3
33003606	STB_CM_INTERBUS-S	0
33003608	STB_CM_MODBUS_PLUS	0
35006657	Schematic Drawing	0
35006769	Schematic Drawing	1
35006884	E30 Schematic	1
35007156	Schematic Drawing	2
35007158	Schematic Drawing	1
BBV2355103	PBA STBNIP2311	4