



Commercial status

End of Commercialisation :

⚠ End of Commercialisation

Main

Range	Multi 9
Product name	Multi 9 PRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	PRD8r
Device application	Distribution
Poles description	2P
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	IT
[Uoc] open circuit voltage	10 KV type 3 common mode L/PE

Complementary

Surge arrester class type	Type 2 + 3
Surge arrester technology	MOV
[Ue] rated operational voltage	230 V AC (+/- 10 %) at 50/60 Hz
Nominal discharge current	Common mode: 2.5 kA (L/PE)
Maximum discharge current	Common mode: 8 kA L/PE
[Uc] maximum continuous operating voltage	Common mode: 460 V L/PE
Maximum [Up] voltage protection level	Common mode <1.5 kV type 2 L/PE
Disconnecter device type	Associated circuit breaker 25 A - Icu 15 kA Associated circuit breaker 25 A - Icu 25 kA Associated circuit breaker 20 A - Icu 10 kA
Signalling circuit voltage	0.25 A/250 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	81 Mm
Width	36 Mm
Depth	69 Mm
Colour	Grey (RAL 7035)
Response time	<= 25 ns
Connections - terminals	Tunnel type terminal (downside) 2.5...35 mm ² Tunnel type terminal (upside) 2.5...35 mm ²
Tightening torque	2.5 N.M

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP40 on front face: conforming to IEC 60529 IP20 on terminal: conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...90 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**