



Main

Range	Masterpact
Range of product	Masterpact NW
Product name	Masterpact NW
Product or component type	Basic frame
Device short name	Masterpact NW40b
Circuit breaker name	Masterpact NW40bH1
Poles description	4P
Neutral position	Right
Network type	AC
Breaking capacity code	H1
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category B

Complementary

Network frequency	50/60 Hz
Control type	Push-button
Mounting mode	Drawout
[In] rated current	4000 A (40 °C)
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	12 kV conforming to IEC 60947-2
[Icm] rated short-circuit making capacity	220 kA 525 V AC 50/60 Hz 220 kA 690 V AC 50/60 Hz
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
Circuit breaker CT rating	4000 A
Breaking capacity	100 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 690 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	Ics 100 kA 525 V AC 50/60 Hz conforming to IEC 60947-2 Ics 100 kA 690 V AC 50/60 Hz conforming to IEC 60947-2
Protection type	Without protection
Mechanical durability	10000 cycles with maintenance conforming to IEC 60947-2 5000 cycles without maintenance conforming to IEC 60947-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Electrical durability	AC-23A : 1500 cycles 440 V AC 50/60 Hz without maintenance conforming- to IEC 60947-2 AC-23A : 1500 cycles 690 V AC 50/60 Hz without maintenance conforming- to IEC 60947-2 AC-3 : 6000 cycles 440/690 V AC 50/60 Hz without maintenance conforming- to IEC 60947-2 1500 cycles 440 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 1500 cycles 690 V AC 50/60 Hz without maintenance conforming to IEC 60947-2
Connection pitch	230 mm
[Icw] rated short-time withstand current	100 kA (1 s) conforming to IEC 60947-2 100 kA (3 s) conforming to IEC 60947-2
Maximum breaking time	25 ms
Closing response time	< 80 ms
Height	479 mm
Width	1016 mm
Depth	394.5 mm
Compatibility code	NW40b

Environment

Standards	IEC 60947-2
Product certifications	ASTA
Pollution degree	4 conforming to IEC 60664-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**