

8536SBA1V02E

Non-Reversing Starter Size 0, 2-Pole, Bi-metallic
Overload, NEMA 12/3R



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product or component type	Starter
Range of product	S
Control circuit	Common control circuit

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	18 A
Poles description	2P
Phase	1 phase
Rated power in HP	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control type	No control units
Thermal overload type	Non-compensated bimetallic 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)


Environment

NEMA degree of protection	NEMA 12
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	13
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Product Life Status : **Commercialised**