



Main

Product or component type	Combination Starter
Range of product	S
Control circuit	Control circuit transformer

Complementary

[Uc] control circuit voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Line Rated Current	27 A
Poles description	3P
Motor power hp	0.25...5 hp 200 V AC 3 phases 0.25...7.5 hp 230 V AC 3 phases 0.25...10 hp 460 V AC 3 phases 0.25...10 hp 575 V AC 3 phases
System Voltage	600 V AC
Control type	Selector switch (HAND-OFF-AUTO)
Local signalling	No indicator
Auxiliary contact composition	1 NO + 1 NC
Provided equipment	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Solid state Motor Logic class 10/20 1.5...4.5 A FLA
Circuit breaker type	EMCP
Disconnecter device type	Circuit breaker 30 A
Breaking capacity	35 kA 600 V AC 100 kA 480 V AC
Height	24 in
Depth	9.84 in
Width	9.5 in
Length	3.25 in

Environment

NEMA degree of protection	NEMA 12 painted sheet steel and with external reset
NEMA size	1
Product certifications	UL listed file E152395 CCN NKJH7 UL listed file E152395 CCN NKJH CSA file 584 class 3211 04

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	48
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Product Life Status : **Commercialised**