

Product data sheet

Characteristics

8539SFW42V06

COMBO STARTER 600VAC 135A NEMA



by Schneider Electric

Price*: 13208.00 USD

Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Contact application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure corrosion resistance indoor/outdoor Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor

Complementary

Rated current	135 A
System Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Depth	10.53 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Brushed stainless steel
Height	52.5 in
Motor power hp	30 hp 200 V AC 60...75 hp 460 V AC 60...100 hp 575 V AC
NEMA size	4
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker KAL3625025M
Product weight	120 lb(US)
Short-circuit protection	22000 A AIR
Thermal overload type	Melting alloy
Width	16 in

Environment

NEMA degree of protection	NEMA 4/4X
Product certifications	UL listed file E152395 CCN NKJH7

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	120
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**