



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E China
Load type	Resistive
Cover plate colour tint	Bronze

Complementary

Device mounting	Flush Surface
Rated current	10 A at 250 V AC 50/60 Hz
Number of gangs	1 gang
Material	Polycarbonate base Polycarbonate cover
Connections - terminals	Screwless terminals
Width	46.8 Mm
Height	45.8 Mm
Depth	36.2 Mm

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %, non-condensing (storage) 10...95 %, non-condensing (operating)
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	GB 2099.1
IP degree of protection	IP20
Standards	GB 2099.1
Product certifications	CCC

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Product Life Status : **End of commerc. - Block**