



by Schneider Electric



### Main

|                           |                 |
|---------------------------|-----------------|
| Range of product          | Harmony 9001SK  |
| Product or component type | Selector switch |
| Device short name         | 9001SK          |
| Type of operator          | Maintained      |

### Complementary

|                               |                       |
|-------------------------------|-----------------------|
| Bezel material                | Plastic               |
| Mounting diameter             | 30 Mm                 |
| Net weight                    | 0.059 Kg              |
| Shape of signaling unit head  | Round                 |
| Operator position information | 3 positions           |
| Contacts type and composition | Without contact block |
| Mechanical durability         | 500000 Cycles         |
| Device presentation           | Basic element         |

### Environment

|                                       |  |
|---------------------------------------|--|
| Protective treatment                  | TC   |
| Ambient air temperature for storage   | -40...70 °C  |
| Ambient air temperature for operation | -25...70 °C  |
| Electrical shock protection class     | Class II conforming to IEC 61140   |
| IP degree of protection               | IP66 conforming to IEC 60529   |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 4X<br>NEMA 6                     |
| Standards                             | EN/IEC 60947-1<br>JIS C 4520<br>CSA C22.2 No 14<br>JIS C 852<br>UL 508<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4 |
| Product certifications                | UL 508<br>NEMA   |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|                      |  |
|----------------------|--|
| Vibration resistance | 7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance     | 50 gn conforming to IEC 60068-2-27               |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                              |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | No need of specific recycling operations  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Product Life Status : **Commercialised**