



by Schneider Electric



Commercial status

End of Commercialisation :

End of Commercialisation

Main

Range of product	9012G
Pressure sensor type	Electromechanical pressure switch
Pressure sensor name	9012G
Pressure sensor size	250 Psi
Maximum pressure	750 psi
Contacts type and composition	NC-NO, SPDT-DB, Form Z, snap action, silver nickel contacts
Controlled fluid	Hydraulic oil (-40...250 °F) Non-corrosive liquids Air Non-corrosive gas
Fluid connection type	0.25 inch BS2779 parallel pipe thread conforming to UL 508
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable differential
Local display	Without

Complementary

Range on decreasing pressure	5...250 Psi
Approx adjustable differential at mid range	10...49 Psi +/- 2.5 % full scale
Cable entry	20 mm BS4568 conduit entrance
Terminal block type	4 screw terminals
Electrical connection	Screw-clamp terminals, AWG 22...AWG 12
Electrical circuit type	Control circuit
Local signalling	1 LED: (clear) 24 V DC
[In] rated current	2.75 A 24 V DC
Setting	Internal
Enclosure material	Die cast aluminium alloy 380
Pressure actuator	Diaphragm nitrile (Buna-N)
Height	5.55 In
Depth	3.11 In
Width	3.5 In
Operating position	Any position
Materials in contact with fluid	Nitrile (Buna-N) Zinc plated steel

Short-circuit protection	10 A cartridge overload and short-circuit protection, type gL
Maximum operating rate	120 Cyc/Mn
Mechanical durability	5000000 Cycles
Repeat accuracy	4 %
Net weight	3 Lb(US)

Environment

Vibration resistance	2 gn (f= 40...150 Hz) conforming to IEC 68-2-6
Shock resistance	50 gn conforming to IEC 58-2-27
Standards	CSA C22.2 No 14 CE UL 508
Product certifications	UL listed file E12158 CCN NKPZ and CCN NTHT CSA LR25490 class 3211 03 CE
NEMA degree of protection	NEMA 4/4X/13 conforming to UL 50
Ambient air temperature for operation	-10...185 °F

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Post commercialisation**