



### Main

Range	PowerPact
Product name	PowerPact B
Device short name	BD 070
Product or component type	Circuit breaker
Device application	Distribution

### Complementary



[In] rated current	70 A
Poles description	4P
Protected poles description	4t
Control type	Toggle
Mounting mode	Clip-on (35 mm symmetrical DIN rail) By screws (plate)
Network type	AC
Network frequency	50/60 Hz
Breaking capacity code	D
Breaking capacity	25 KA at 240 V AC 50/60 Hz conforming to UL 489 18 KA at 480 V AC 50/60 Hz conforming to UL 489 Icu 25 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 Icu 14 kA at 500...525 V AC 50/60 Hz conforming to IEC 60947-2 18 KA at 480Y/277 V AC 50/60 Hz conforming to UL 489 14 KA at 600Y/347 V AC 50/60 Hz conforming to UL 489 25 KA at 208Y/120 V AC 50/60 Hz conforming to UL 489 Icu 18 kA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 Icu 18 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	25 KA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 14 KA at 500...525 V AC 50/60 Hz conforming to IEC 60947-2 18 KA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 18 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 KV IEC 60947-2
[Ui] rated insulation voltage	800 V conforming to IEC 60947-2
Trip unit technology	Thermal-magnetic
Trip unit name	TM-D
Trip unit protection functions	LI
Protection type	Short-circuit protection (magnetic) Overload protection (thermal)
Trip unit rating	70 A at 40 °C
Magnetic hold current	640 A

Magnetic tripping current	960 A
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A
Mechanical durability	15000 Cycles conforming to IEC 947-1 Annex K ed 5.2
Electrical durability	10000 Cycles conforming to IEC 947-1 Annex K ed 5.2 for In at 440 V
Connection pitch	27 Mm
Local signalling	Flag (green)presence of auxiliary contacts:
Rotary handle padlocking	Padlock in OFF or ON position
Connections - terminals	Upside compression lug/busbar Downside compression lug/busbar
Thread type	M6
Thickness	6.5 Mm
Tightening torque	5 N.M for 2.5...16 mm <sup>2</sup> (AWG 14...AWG 4) 9 N.M for 25...95 mm <sup>2</sup> (AWG 3...AWG 3/0)
Number of slots	1 slot(s) for auxiliary switch OF (plug-in) 1 slot(s) for voltage release MN or MX (plug-in) 1 slot(s) for alarm switch SD (plug-in)
Wire stripping length	20 Mm
Quality labels	CE
Standards	EN/IEC 60947-5-1 CSA C22.2 No 5 NEMA AB1 GB 14048.2 NMJ J-266 EN/IEC 60947-2 UL 489
Colour	Grey (RAL 7016)
9 mm pitches	12
Height	137 Mm
Width	108 Mm
Depth	80 Mm
Net weight	1.241 Kg
Quantity per set	Set of 1

## Environment

Product certifications	UL IEC CCC EAC CSA NOM
IP degree of protection	Front cover: IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C
Operating altitude	2000 m without derating 5000 m with derating

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**