




by Schneider Electric



Main

| | |
|------------------------------|----------------------|
| Range of product | Square D Pumptrol |
| Product or component type | Float switch |
| Device application | Closed tank |
| Device short name | 9037H |
| Product specific application | Liquid level control |
| Electrical circuit type | Power circuit |
| Quantity per set | Set of 1 |
| Type of packing | Individual |

Complementary

| | |
|-------------------------------|---|
| Product destination | For closed tank |
| Device mounting | Screw-in bushing |
| Cable entry number | 2 conduit entries for 3/4"-14 NPT UL 508 |
| Contacts type and composition | 2 NC snap action DPST-DB Form YY |
| Controlled fluid | Fresh water @ specific gravity of 0.85 in or higher 0...220 °F Sea water @ specific gravity of 0.85 in or higher 0...220 °F Hydraulic oil @ specific gravity of 0.85 in or higher 0...220 °F Corrosive fluid @ specific gravity of 0.85 in or higher 0...220 °F |
| Motor power kW | 1.5 kW 2 hp @ 115 V AC 1 phase 2.2 kW 3 hp @ 115 V AC 3 phases 2.2 kW 3 hp @ 230 V AC 1 phase 3.7 kW 5 hp @ 230 V AC 3 phases 0.75 kW 1 hp @ 460 V AC 3 phases 0.75 kW 1 hp @ 475 V AC 3 phases 0.18 kW 0.25 hp @ 32 V DC 0.37 kW 0.5 hp @ 115 V DC 0.37 kW 0.5 hp @ 230 V DC |
| Electrical connection | Screw-clamp terminals 10 AWG |
| Contact operation | Contacts close on liquid rise |
| Float movement | 2.5...5 in adjustable |
| Float position | Right |
| Float rod angle | 90° (offset) |
| Short-circuit protection | Cartridge fuse gG |
| Local signalling | With external pointer |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|---------------------------------|--|
| Materials in contact with fluid | Cast iron 316 stainless steel Nitrile (Buna-N) or equivalent rubber Yellow brass 304 stainless steel |
| Enclosure material | Cast aluminium |
| Operating position | Vertical position only |
| Electrical durability | 100 cycles @ 60 cyc/mn |
| Mechanical durability | 300 cycles |
| Terminal block type | 4 terminals |
| Operating rate | 60 cyc/mn |
| [Ui] rated insulation voltage | 575 V UL 508 |
| Terminals description ISO n°1 | Line-load-load-line |
| Factory modification | Without |
| Kit composition | Float Rod Float switch |

Environment

| | |
|---------------------------------------|---|
| Standards | CE UL 508 |
| Ambient air temperature for operation | -22...220 °F |
| Ambient air temperature for storage | -22...220 °F |
| NEMA degree of protection | NEMA 7/9 UL 698 |
| Product certifications | UL listed file E12443 CSA file LR26817 |

Offer Sustainability

| | |
|----------------------------------|---|
| RoHS (date code: YYWW) | Will not be compliant |
| REACH | Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Available End Of Life Information |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Product Life Status : **Commercialised**