



Main

Range of product	ProDis
Range	Prodis
Product name	DT60
Product or component type	Miniature circuit-breaker
Device short name	DT60N
Device application	Distribution
Poles description	3P + N
Number of protected poles	4
Neutral position	Left
[In] rated current	40 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6000 A Icn at 400 V AC 50 Hz conforming to EN/IEC 60898-1 10 KA Icu at 400...415 V AC 50 Hz conforming to IEC 60947-2
Suitability for isolation	Yes
Quality labels	NF

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	230 V AC 50/60 Hz between phase and neutral 400 V AC 50/60 Hz between phases
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6000 A 100 % x Icn at 400 V AC 50 Hz conforming to EN/IEC 60898-1 7.5 KA 75 % x Icu at 400...415 V AC 50 Hz conforming to IEC 60947-2
Limitation class	3 conforming to EN/IEC 60898-1
[Ui] rated insulation voltage	400 V AC 50 Hz
[Uimp] rated impulse withstand voltage	6 KV conforming to IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	81 Mm
Width	72 Mm

Depth	78 Mm
Net weight	440 G
Colour	White
Mechanical durability	20000 Cycles
Electrical durability	10000 Cycles
Locking options description	Padlocking device
Connections - terminals	Tunnel type terminals0.5...25 mm ² flexible Tunnel type terminals0.5...35 mm ² rigid
Wire stripping length	13 Mm
Tightening torque	3.5 N.M
Earth-leakage protection	Separate block

Environment

Standards	EN/IEC 60898-1 EN/IEC 60947-2
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**