



Main

Range	PowerPact
Product name	PowerPact B
Device short name	BD 100
Product or component type	Circuit breaker
Device application	Distribution

Complementary

[In] rated current	100 A
Poles description	1P
Protected poles description	1t
Control type	Toggle
Mounting mode	Clip-on (35 mm symmetrical DIN rail) By screws (plate)
Network type	AC
Network frequency	50/60 Hz
Breaking capacity code	D
Breaking capacity	25 KA at 240 V AC 50/60 Hz conforming to UL 489 Icu 25 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 18 KA at 480Y/277 V AC 50/60 Hz conforming to UL 489 14 KA at 600Y/347 V AC 50/60 Hz conforming to UL 489 25 KA at 208Y/120 V AC 50/60 Hz conforming to UL 489
[Ue] rated operational voltage	240 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	25 KA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 KV IEC 60947-2
[Ui] rated insulation voltage	800 V conforming to IEC 60947-2
Trip unit technology	Thermal-magnetic
Trip unit name	TM-D
Trip unit protection functions	LI
Protection type	Overload protection (thermal) Short-circuit protection (magnetic)
Trip unit rating	100 A at 40 °C
Magnetic hold current	1000 A
Magnetic tripping current	1500 A
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A
Mechanical durability	15000 Cycles conforming to IEC 947-1 Annex F ed 5.2
Electrical durability	10000 Cycles conforming to IEC 947-1 Annex K ed 5.2 for In at 240 V

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connection pitch	27 Mm
Rotary handle padlocking	Padlock in OFF or ON position
Connections - terminals	Downside 1 Everlink lug wire size 2.5...70 mm ² (AWG 14...AWG 2/0), fine stranded copper Upside 1 Everlink lug wire size 2.5...95 mm ² (AWG 14...AWG 3/0), rigid or stranded aluminium/copper
Tightening torque	5 N.M for 2.5...16 mm ² (AWG 14...AWG 4) 9 N.M for 25...95 mm ² (AWG 3...AWG 3/0)
Wire stripping length	20 Mm
Quality labels	CE
Standards	GB 14048.2 EN/IEC 60947-5-1 UL 489 CSA C22.2 No 5 NEMA AB1 EN/IEC 60947-2 NMX J-266
Colour	Grey (RAL 7016)
9 mm pitches	3
Height	137 Mm
Width	27 Mm
Depth	80 Mm
Net weight	0.51 Kg
Quantity per set	Set of 1

Environment

Product certifications	UL IEC CCC EAC CSA NOM
IP degree of protection	Front cover: IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C
Operating altitude	2000 m without derating 5000 m with derating

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**