



### Main

Range of product	ProDis
Range	Prodis
Product name	DT60
Product or component type	Miniature circuit-breaker
Device short name	DT60N
Device application	Distribution
Poles description	3P + N
Number of protected poles	4
Neutral position	Left
[In] rated current	63 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6000 A Icn at 400 V AC 50 Hz conforming to EN/IEC 60898-1 10 KA Icu at 400...415 V AC 50 Hz conforming to IEC 60947-2
Suitability for isolation	Yes
Quality labels	NF

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	230 V AC 50/60 Hz between phase and neutral 400 V AC 50/60 Hz between phases
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6000 A 100 % x Icn at 400 V AC 50 Hz conforming to EN/IEC 60898-1 7.5 KA 75 % x Icu at 400...415 V AC 50 Hz conforming to IEC 60947-2
Limitation class	3 conforming to EN/IEC 60898-1
[Ui] rated insulation voltage	400 V AC 50 Hz
[Uimp] rated impulse withstand voltage	6 KV conforming to IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	81 Mm
Width	72 Mm

Depth	78 Mm
Net weight	440 G
Colour	White
Mechanical durability	20000 Cycles
Electrical durability	10000 Cycles
Locking options description	Padlocking device
Connections - terminals	Tunnel type terminals0.5...25 mm <sup>2</sup> flexible Tunnel type terminals0.5...35 mm <sup>2</sup> rigid
Wire stripping length	13 Mm
Tightening torque	3.5 N.M
Earth-leakage protection	Separate block

## Environment

Standards	EN/IEC 60898-1 EN/IEC 60947-2
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**