

Product data sheet

Characteristics

BMH2053P22F1A

servo motor BMH - 84 Nm - 3800 rpm - untapped shaft - with brake - IP65/IP67



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 8410.00 USD



Main

Product or component type	Servo motor
Device short name	BMH
Maximum mechanical speed	3800 Rpm
Continuous stall torque	743.46 Lbf.In (84 N.m) LXM32.D72N4 24 A, 400 V, three phase 743.46 Lbf.In (84 N.m) LXM32.D72N4 24 A, 480 V, three phase
Peak stall torque	2053.37 Lbf.In (232 N.m) LXM32.D72N4 24 A, 400 V, three phase 2053.37 Lbf.In (232 N.m) LXM32.D72N4 24 A, 480 V, three phase
Nominal output power	6500 W LXM32.D72N4 24 A, 400 V, three phase 6500 W LXM32.D72N4 24 A, 480 V, three phase
Nominal torque	462.01 Lbf.In (52.2 N.m) LXM32.D72N4 24 A, 400 V, three phase 462.01 Lbf.In (52.2 N.m) LXM32.D72N4 24 A, 480 V, three phase
Nominal speed	1200 rpm LXM32.D72N4 24 A, 400 V, three phase 1200 rpm LXM32.D72N4 24 A, 480 V, three phase
Product compatibility	LXM32.D72N4 400...480 V three phase
Shaft end	Smooth shaft
IP degree of protection	IP65 standard IP67 with IP67 kit
Speed feedback resolution	131072 points/turn x 4096 turns
Holding brake	With
Mounting support	International standard flange
Electrical connection	Straight connectors

Complementary

Range compatibility	Lexium 32
[Us] rated supply voltage	480 V
Phase	Three phase
Continuous stall current	25.2 A
Continuous power	9.6 W
Maximum current Irms	72 A LXM32.D72N4
Maximum permanent current	107.4 A
Second shaft	Without second shaft end

Shaft diameter	1.50 In (38 mm)
Shaft length	3.15 In (80 mm)
Feedback type	Multiturn SinCos Hiperface
Holding torque	708.06 Lbf.In (80 N.m) holding brake
Motor flange size	8.07 In (205 mm)
Number of motor stacks	3
Torque constant	3.5 N.M/A 248 °F (120 °C)
Back emf constant	218 V/Krpm 248 °F (120 °C)
Number of motor poles	10
Rotor inertia	206 Kg.Cm ²
Stator resistance	0.32 Ohm 68 °F (20 °C)
Stator inductance	6.9 MH 68 °F (20 °C)
Stator electrical time constant	21.6 Ms 68 °F (20 °C)
Maximum radial force Fr	4500 N 1000 rpm 3570 N 2000 rpm 3120 N 3000 rpm
Maximum axial force Fa	0.2 x Fr
Brake pull-in power	40 W
Type of cooling	Natural convection
Length	21.20 In (538.5 mm)
Centring collar diameter	7.09 In (180 mm)
Centring collar depth	0.16 In (4 mm)
Number of mounting holes	4
Mounting holes diameter	0.55 In (14 mm)
Circle diameter of the mounting holes	8.46 In (215 mm)
Net weight	158.51 Lb(US) (71.9 kg)

Ordering and shipping details

Category	18282 - LEXIUM 32 MOTORS
Discount Schedule	PC53
GTIN	03606485202143
Nbr. of units in pkg.	1
Package weight(Lbs)	165 Lb(US) (74.84 kg)
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	14.17 In (36 cm)
Package 1 width	12.20 In (31 cm)
Package 1 Length	28.74 In (73 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive-harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure [Product Environmental Profile](#)

WEEE The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty 18 months

Product Life Status : **Commercialised**

BMH2053P22F1A may be replaced by any of the following products:



BMH2053P32F2A

servo motor BMH - 84 Nm - 3800 rpm - keyed shaft - with brake - IP65/IP67

Qty 1

Reason for Substitution: End of life | Substitution date: 02 Apr 2020 | Linking to group 1
