



by Schneider Electric



Main

Range	PowerPact
Product name	PowerPact B
Device short name	BJ 040
Product or component type	Circuit breaker
Device application	Distribution

Complementary





[In] rated current	40 A
Poles description	1P
Protected poles description	1t
Control type	Toggle
Mounting mode	Clip-on (35 mm symmetrical DIN rail) By screws (plate)
Network type	AC
Network frequency	50/60 Hz
Breaking capacity code	J
Breaking capacity	100 KA at 240 V AC 50/60 Hz conforming to UL 489 Icu 100 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 65 KA at 480Y/277 V AC 50/60 Hz conforming to UL 489 25 KA at 600Y/347 V AC 50/60 Hz conforming to UL 489 100 KA at 208Y/120 V AC 50/60 Hz conforming to UL 489
[Ue] rated operational voltage	240 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	65 KA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 KV IEC 60947-2
[Ui] rated insulation voltage	800 V conforming to IEC 60947-2
Trip unit technology	Thermal-magnetic
Trip unit name	TM-D
Trip unit protection functions	LI
Protection type	Overload protection (thermal) Short-circuit protection (magnetic)
Trip unit rating	40 A at 40 °C
Magnetic hold current	400 A
Magnetic tripping current	600 A
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A

Mechanical durability	15000 Cycles conforming to IEC 947-1 Annex F ed 5.2
Electrical durability	10000 Cycles conforming to IEC 947-1 Annex K ed 5.2 for In at 240 V
Connection pitch	27 Mm
Rotary handle padlocking	Padlock in OFF or ON position
Connections - terminals	Downside 1 Everlink lug wire size 2.5...70 mm ² (AWG 14...AWG 2/0), fine stranded copper Upside 1 Everlink lug wire size 2.5...95 mm ² (AWG 14...AWG 3/0), rigid or stranded aluminium/copper
Tightening torque	5 N.M for 2.5...16 mm ² (AWG 14...AWG 4) 9 N.M for 25...95 mm ² (AWG 3...AWG 3/0)
Wire stripping length	20 Mm
Quality labels	CE
Standards	EN/IEC 60947-2 CSA C22.2 No 5 GB 14048.2 EN/IEC 60947-5-1 NMX J-266 UL 489 NEMA AB1
Colour	Grey (RAL 7016)
9 mm pitches	3
Height	137 Mm
Width	27 Mm
Depth	80 Mm
Net weight	0.51 Kg
Quantity per set	Set of 1

Environment

Product certifications	UL IEC CCC EAC CSA NOM
IP degree of protection	Front cover: IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C
Operating altitude	2000 m without derating 5000 m with derating

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**