



Main

Product or component type	Servo motor
Device short name	BSH
Maximum mechanical speed	6000 Rpm
Continuous stall torque	3.4 N.M for LXM05AD14N4, 380...480 V, three phase 3.4 N.M for LXM05BD14N4, 380...480 V, three phase 3.4 N.M for LXM05CD14N4, 380...480 V, three phase
Peak stall torque	7.1 N.M for LXM05AD14N4, 380...480 V, three phase 7.1 N.M for LXM05BD14N4, 380...480 V, three phase 7.1 N.M for LXM05CD14N4, 380...480 V, three phase
Nominal output power	500 W for LXM05AD14N4, 380...480 V, three phase 500 W for LXM05BD14N4, 380...480 V, three phase 500 W for LXM05CD14N4, 380...480 V, three phase
Nominal torque	3.16 N.M for LXM05AD14N4, 380...480 V, three phase 3.16 N.M for LXM05BD14N4, 380...480 V, three phase 3.16 N.M for LXM05CD14N4, 380...480 V, three phase
Nominal speed	1500 rpm for LXM05AD14N4, 380...480 V, three phase 1500 rpm for LXM05BD14N4, 380...480 V, three phase 1500 rpm for LXM05CD14N4, 380...480 V, three phase
Product compatibility	LXM05AD14N4 at 380...480 V three phase LXM05BD14N4 at 380...480 V three phase LXM05CD14N4 at 380...480 V three phase
Shaft end	Untapped
IP degree of protection	IP50 standard
Speed feedback resolution	131072 points/turn
Holding brake	Without
Mounting support	International standard flange
Electrical connection	Rotatable right-angled connectors

Complementary

Range compatibility	Lexium 05
[Us] rated supply voltage	480 V
Network number of phases	Three phase
Continuous stall current	1.8 A
Continuous power	1.6 W
Maximum current Irms	6.3 A for LXM05AD14N4 6.3 A for LXM05BD14N4 6.3 A for LXM05CD14N4
Maximum permanent current	6.3 A
Switching frequency	4 kHz
Second shaft	Without second shaft end
Shaft diameter	19 Mm

Shaft length	40 Mm
Feedback type	Single turn SinCos Hiperface
Motor flange size	100 Mm
Torque constant	1.83 N.M/A at 120 °C
Back emf constant	115 V/Krpm at 120 °C
Number of motor poles	8
Rotor inertia	1.4 Kg.Cm ²
Stator resistance	13.9 Ohm at 20 °C
Stator inductance	64.3 MH at 20 °C
Stator electrical time constant	4.63 Ms at 20 °C
Maximum radial force Fr	530 N at 5000 rpm 570 N at 4000 rpm 630 N at 3000 rpm 720 N at 2000 rpm 900 N at 1000 rpm
Maximum axial force Fa	0.2 x Fr
Type of cooling	Natural convection
Length	168.5 Mm
Centring collar diameter	95 Mm
Centring collar depth	3.5 Mm
Number of mounting holes	4
Mounting holes diameter	9 Mm
Circle diameter of the mounting holes	115 Mm
Net weight	4.2 Kg

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**