



by Schneider Electric



Main

Range	PowerPact
Product name	PowerPact B
Device short name	BJ 090
Product or component type	Circuit breaker
Device application	Distribution

Complementary

[In] rated current	90 A
Poles description	4P
Protected poles description	4t
Control type	Toggle
Mounting mode	Clip-on (35 mm symmetrical DIN rail) By screws (plate)
Network type	AC
Network frequency	50/60 Hz
Breaking capacity code	J
Breaking capacity	100 KA at 240 V AC 50/60 Hz conforming to UL 489 65 KA at 480 V AC 50/60 Hz conforming to UL 489 Icu 100 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 Icu 25 kA at 500...525 V AC 50/60 Hz conforming to IEC 60947-2 Icu 10 kA at 690 V AC 50/60 Hz conforming to IEC 60947-2 65 KA at 480Y/277 V AC 50/60 Hz conforming to UL 489 25 KA at 600Y/347 V AC 50/60 Hz conforming to UL 489 100 KA at 208Y/120 V AC 50/60 Hz conforming to UL 489 Icu 65 kA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 Icu 65 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	100 KA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 25 KA at 500...525 V AC 50/60 Hz conforming to IEC 60947-2 10 KA at 690 V AC 50/60 Hz conforming to IEC 60947-2 65 KA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 65 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 KV IEC 60947-2
[Ui] rated insulation voltage	800 V conforming to IEC 60947-2
Trip unit technology	Thermal-magnetic
Trip unit name	TM-D
Trip unit protection functions	LI

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Protection type	Short-circuit protection (magnetic) Overload protection (thermal)
Trip unit rating	90 A at 40 °C
Magnetic hold current	1000 A
Magnetic tripping current	1500 A
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A
Mechanical durability	15000 Cycles conforming to IEC 947-1 Annex K ed 5.2
Electrical durability	10000 Cycles conforming to IEC 947-1 Annex K ed 5.2 for In at 440 V
Connection pitch	27 Mm
Local signalling	Flag (green)presence of auxiliary contacts:
Rotary handle padlocking	Padlock in OFF or ON position
Connections - terminals	Upside 1 EverLink lug with voltage tap-off wire size 2.5...70 mm ² (AWG 14...AWG 2/0), fine stranded copper Downside 1 Everlink lug wire size 2.5...70 mm ² (AWG 14...AWG 2/0), fine stranded copper Upside 1 EverLink lug with voltage tap-off wire size 2.5...95 mm ² (AWG 14...AWG 3/0), rigid or stranded aluminium/copper Downside 1 Everlink lug wire size 2.5...95 mm ² (AWG 14...AWG 3/0), rigid or stranded aluminium/copper
Current of common	10 A for 0.5...6 mm ² (AWG 20...AWG 10), stranded or fine stranded 10 A for 1.5...6 mm ² (AWG 20...AWG 10), rigid
Tightening torque	5 N.M for 2.5...16 mm ² (AWG 14...AWG 4) 9 N.M for 25...95 mm ² (AWG 3...AWG 3/0)
Number of slots	1 slot(s) for auxiliary switch OF (plug-in) 1 slot(s) for voltage release MN or MX (plug-in) 1 slot(s) for alarm switch SD (plug-in)
Wire stripping length	20 Mm
Quality labels	CE
Standards	EN/IEC 60947-5-1 GB 14048.2 EN/IEC 60947-2 NMJ J-266 UL 489 CSA C22.2 No 5 NEMA AB1
Colour	Grey (RAL 7016)
9 mm pitches	12
Height	137 Mm
Width	108 Mm
Depth	80 Mm
Net weight	1.441 Kg
Quantity per set	Set of 1

Environment

Product certifications	UL IEC CCC EAC CSA NOM
IP degree of protection	Front cover: IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C
Operating altitude	2000 m without derating 5000 m with derating

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**