

# Product data sheet

## Characteristics

# BMH0703T06A1A

servo motor BMH - 3.4 Nm - 8000 rpm - untapped shaft - without brake - IP54



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 860.00 USD



### Main

Product or component type	Servo motor
Device short name	BMH
Maximum mechanical speed	8000 Rpm
Continuous stall torque	30.09 Lbf.In (3.4 N.m) LXM32.D30M2 10 A, 115 V, single phase 30.09 Lbf.In (3.4 N.m) LXM32.D18M2 6 A, 230 V, single phase
Peak stall torque	77.00 Lbf.In (8.7 N.m) LXM32.D30M2 10 A, 115 V, single phase 90.28 Lbf.In (10.2 N.m) LXM32.D18M2 6 A, 230 V, single phase
Nominal output power	650 W LXM32.D30M2 10 A, 115 V, single phase 900 W LXM32.D18M2 6 A, 230 V, single phase
Nominal torque	27.44 Lbf.In (3.1 N.m) LXM32.D30M2 10 A, 115 V, single phase 25.67 Lbf.In (2.9 N.m) LXM32.D18M2 6 A, 230 V, single phase
Nominal speed	2000 rpm LXM32.D30M2 10 A, 115 V, single phase 3000 rpm LXM32.D18M2 6 A, 230 V, single phase
Product compatibility	LXM32.D30M2 115 V single phase LXM32.D18M2 230 V single phase
Shaft end	Smooth shaft
IP degree of protection	IP54 standard
Speed feedback resolution	32768 points/turn
Holding brake	Without
Mounting support	International standard flange
Electrical connection	Straight connectors

### Complementary

Range compatibility	Lexium 32
[Us] rated supply voltage	240 V
Phase	Three phase
Continuous stall current	5.55 A
Continuous power	1.68 W
Maximum current Irms	15 A LXM32.D30M2 17.8 A LXM32.D18M2
Maximum permanent current	17.84 A

Second shaft	Without second shaft end
Shaft diameter	0.55 In (14 mm)
Shaft length	1.18 In (30 mm)
Feedback type	Single turn SinCos Hiperface
Motor flange size	2.76 In (70 mm)
Number of motor stacks	3
Torque constant	0.61 N.M/A 248 °F (120 °C)
Back emf constant	39.3 V/Krpm 248 °F (120 °C)
Number of motor poles	10
Rotor inertia	1.67 Kg.Cm <sup>2</sup>
Stator resistance	1.32 Ohm 68 °F (20 °C)
Stator inductance	4.3 MH 68 °F (20 °C)
Stator electrical time constant	3.3 Ms 68 °F (20 °C)
Maximum radial force Fr	730 N 1000 rpm 580 N 2000 rpm 510 N 3000 rpm 460 N 4000 rpm 430 N 5000 rpm 400 N 6000 rpm
Maximum axial force Fa	0.2 x Fr
Type of cooling	Natural convection
Length	7.32 In (186 mm)
Centring collar diameter	2.36 In (60 mm)
Centring collar depth	0.10 In (2.5 mm)
Number of mounting holes	4
Mounting holes diameter	0.22 In (5.5 mm)
Circle diameter of the mounting holes	3.23 In (82 mm)
Net Weight	6.61 Lb(US) (3 kg)

## Ordering and shipping details

Category	18282 - LEXIUM 32 MOTORS
Discount Schedule	PC53
GTIN	03606485195087
Nbr. of units in pkg.	1
Package weight(Lbs)	4.3 Lb(US) (1.95 kg)
Returnability	No
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.33 In (11 cm)
Package 1 width	7.87 In (20 cm)
Package 1 Length	15.75 In (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive-harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

---

**Contractual warranty**


---

Warranty	18 months
----------	-----------

---

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)

Dimensions in mm

Straight connector		Rotatable angled		c (without brake)	c (with brake)	c1	c2	c3	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2									
39.5	25.5	39.5	39.5	186	225	30	20	5	5 h9	16 <sup>+0</sup> <sub>-0.13</sub>	14 k6	M5 x 17


Dimensions in in.

Straight connector		Rotatable angled		c (without brake)	c (with brake)	c1	c2	c3	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2									
1.55	1	1.55	1.55	7.32	8.85	1.18	0.78	0.19	0.20 h9	0.63 <sup>+0</sup> <sub>-0.0051</sub>	0.55 k6	M5 x 0.67

115 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D30M2 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

Product Life Status : **Commercialised**

BMH0703T06A1A may be replaced by any of the following products:



BMH0703T31A2A

servo motor BMH - 3.4 Nm - 8000 rpm - keyed shaft - without brake - IP65/IP67

Qty 1

Reason for Substitution: End of life | Substitution date: 02 Apr 2020 | Linking to group 1