



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Product or component type	Servo motor
Device short name	BSH
Maximum mechanical speed	6000 Rpm
Continuous stall torque	7.76 N.M for LXM15LD10N4, 400 V, three phase 7.76 N.M for LXM15LD17N4, 230 V, three phase 7.76 N.M for LXM15LD17N4, 400 V, three phase 7.76 N.M for LXM15LD17N4, 480 V, three phase 7.8 N.M for LXM05AD22N4, 380...480 V, three phase 7.8 N.M for LXM05BD22N4, 380...480 V, three phase 7.8 N.M for LXM05CD22N4, 380...480 V, three phase
Peak stall torque	15.19 N.M for LXM15LD10N4, 400 V, three phase 22.95 N.M for LXM15LD17N4, 230 V, three phase 22.95 N.M for LXM15LD17N4, 400 V, three phase 22.95 N.M for LXM15LD17N4, 480 V, three phase 23.17 N.M for LXM05AD22N4, 380...480 V, three phase 23.17 N.M for LXM05BD22N4, 380...480 V, three phase 23.17 N.M for LXM05CD22N4, 380...480 V, three phase
Nominal output power	1400 W for LXM15LD17N4, 480 V, three phase 750 W for LXM15LD17N4, 230 V, three phase 1300 W for LXM15LD10N4, 400 V, three phase 1100 W for LXM05AD22N4, 380...480 V, three phase 1100 W for LXM05BD22N4, 380...480 V, three phase 1100 W for LXM05CD22N4, 380...480 V, three phase 1400 W for LXM15LD17N4, 400 V, three phase
Nominal torque	6.36 N.M for LXM15LD10N4, 400 V, three phase 6.5 N.M for LXM15LD17N4, 400 V, three phase 6.5 N.M for LXM15LD17N4, 480 V, three phase 6.73 N.M for LXM05AD22N4, 380...480 V, three phase 6.73 N.M for LXM05BD22N4, 380...480 V, three phase 6.73 N.M for LXM05CD22N4, 380...480 V, three phase 7 N.M for LXM15LD17N4, 230 V, three phase
Nominal speed	1000 rpm for LXM15LD17N4, 230 V, three phase 1500 rpm for LXM05AD22N4, 380...480 V, three phase 1500 rpm for LXM05BD22N4, 380...480 V, three phase 1500 rpm for LXM05CD22N4, 380...480 V, three phase 2000 rpm for LXM15LD10N4, 400 V, three phase 2000 rpm for LXM15LD17N4, 400 V, three phase 2000 rpm for LXM15LD17N4, 480 V, three phase
Product compatibility	LXM15LD10N4 at 400 V three phase LXM15LD17N4 at 230 V three phase LXM05AD22N4 at 380...480 V three phase LXM05BD22N4 at 380...480 V three phase LXM05CD22N4 at 380...480 V three phase LXM15LD17N4 at 400 V three phase LXM15LD17N4 at 480 V three phase




The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Shaft end	Untapped
IP degree of protection	IP65 standard IP67 with IP67 kit
Speed feedback resolution	131072 points/turn
Holding brake	Without
Mounting support	International standard flange
Electrical connection	Rotatable right-angled connectors

Complementary

Range compatibility	Lexium 05 Lexium 15
[Us] rated supply voltage	480 V
Network number of phases	Three phase
Continuous stall current	3.4 A
Continuous power	3.14 W
Maximum current Irms	15.6 A for LXM15LD10N4 15.6 A for LXM15LD17N4 14.7 A for LXM05AD22N4 14.7 A for LXM05BD22N4 14.7 A for LXM05CD22N4
Maximum permanent current	14.7 A
Switching frequency	4 kHz
Second shaft	Without second shaft end
Shaft diameter	19 Mm
Shaft length	40 Mm
Feedback type	Single turn SinCos Hiperface
Motor flange size	100 Mm
Torque constant	2.22 N.M/A at 120 °C
Back emf constant	1.44 V/Krpm at 120 °C 148 V/Krpm at 120 °C
Number of motor poles	8
Rotor inertia	3.22 Kg.Cm ²
Stator resistance	5.3 Ohm at 20 °C
Stator inductance	32.5 MH at 20 °C 33.7 MH at 20 °C
Stator electrical time constant	6.13 Ms at 20 °C 6.36 Ms at 20 °C
Maximum radial force Fr	1050 N at 1000 rpm 660 N at 4000 rpm 730 N at 3000 rpm 830 N at 2000 rpm
Maximum axial force Fa	0.2 x Fr
Type of cooling	Natural convection
Length	240.5 Mm
Centring collar diameter	95 Mm
Centring collar depth	3.5 Mm
Number of mounting holes	4
Mounting holes diameter	9 Mm
Circle diameter of the mounting holes	115 Mm
Net weight	7.4 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	End of commercialisation
-----------------------	---------------------------------