



### Commercial status

This Product is Obsolete :

 This Product is Obsolete

### Main

Range of product	TeSys D control relay
Range	TeSys
Product name	TeSys CAD
Product or component type	Control relay
Device short name	CAD
Contacting application	Control circuit

### Complementary

Utilisation category	AC-14 DC-13 AC-15
Pole contact composition	3 NO + 2 NC
System Voltage	≤ 690 V AC 25...400 Hz
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	480 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
[Ith] conventional free air thermal current	10 A at ≤ 140 °F (60 °C)
Irms rated making capacity	140 A AC conforming to IEC 60947-5-1 250 A DC conforming to IEC 60947-5-1
[Icw] rated short-time withstand current	100 A 1 s 120 A 500 ms 140 A 100 ms
Associated fuse rating	10 A gG conforming to IEC 60947-5-1
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1 600 V certifications UL 600 V certifications CSA
Mounting support	Plate Rail

Connections - terminals	Spring terminals 1 cable(s) 0...0 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) - cable stiffness: flexible - without cable end Spring terminals 2 cable(s) 0...0 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) - cable stiffness: flexible - without cable end Spring terminals 1 cable(s) 0...0 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) - cable stiffness: solid - without cable end Spring terminals 2 cable(s) 0...0 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) - cable stiffness: solid - without cable end
Control circuit voltage limits	0.3...0.6 Uc drop-out 0.8...1.1 Uc operational 50 Hz 0.85...1.1 Uc operational 60 Hz
Operating time	4...19 ms coil energisation and NC opening 12...22 ms coil energisation and NO closing 4...12 ms coil de-energisation and NO opening 6...17 ms coil de-energisation and NC closing
Mechanical durability	30 Mcycles
Operating rate	180 cyc/mn
Inrush power in VA	70 VA at 68 °F (20 °C) 50 Hz
Hold-in power consumption in VA	8 VA at 68 °F (20 °C) 50 Hz
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non-overlap time	1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact)
Insulation resistance	> 10 MOhm
Mechanical robustness	Shocks control relay open 10 Gn for 11 ms IEC 60068-2-27 Shocks control relay closed 15 Gn for 11 ms IEC 60068-2-27 Vibrations control relay open 2 Gn, 5...300 Hz IEC 60068-2-6 Vibrations control relay closed 4 Gn, 5...300 Hz IEC 60068-2-6
Height	3.9 in (99 mm)
Width	1.77 in (45 mm)
Depth	3.31 in (84 mm)
Product weight	1.28 lb(US) (0.58 kg)
Compatibility code	CAD


## Environment

Standards	VDE 0660 IEC 60947-5-1 NF C 63-140 BS 4794 EN 60947-5
Product certifications	CSA UL
IP degree of protection	IP2x front face conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating

## Ordering and shipping details

Category	22371 - RELAYS, CONTROL
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	1.28
Returnability	N
Country of origin	FR

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
- - - - - Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	<b>End of commercialisation</b>
-----------------------	---------------------------------