



Main

Range	TeSys
Product name	TeSys F
Product or component type	Magnetic latching contactor
Device short name	CR1F
Device application	Control
Contactor application	Motor control Resistive load
Utilisation category	AC-3 AC-1 AC-4
Poles description	3P
Pole contact composition	3 NO
[Ue] rated operational voltage	1000 V AC 25...200 Hz
[Ie] rated operational current	185 A (at <40 °C) at <= 440 V AC AC-3 275 A (at <40 °C) at <= 440 V AC AC-1 170 A (at <40 °C) at <= 440 V AC AC-4
Motor power kW	90 KW at 400 V AC 50/60 Hz (AC-4)
Control circuit type	AC at 50...400 Hz DC standard
[Uc] control circuit voltage	127 V AC 50...400 Hz 127 V DC
Irms rated making capacity	2100 A
Rated breaking capacity	1800 A at 220...440 V 1600 A at 500 V 600 A at 1000 V 1200 A at 660/690 V
[Icw] rated short-time withstand current	1500 A 40 °C - 1 s 1500 A 40 °C - 5 s 1500 A 40 °C - 10 s 920 A 40 °C - 30 s 740 A 40 °C - 1 min 500 A 40 °C - 3 min 400 A 40 °C - 10 min
Associated fuse rating	200 A aM at <= 440 V 315 A BS88 at <= 440 V 315 A gG at <= 440 V
Average impedance	0.36 MOhm - Ith 275 A 50 Hz
[Ui] rated insulation voltage	1000 V conforming to IEC 60158-1 1000 V conforming to IEC 60947-4 1000 V conforming to BS 775 1500 V conforming to VDE 0110 group C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Power dissipation per pole	12 W AC-3 26 W AC-1
Connections - terminals	Bars 2 cable(s) - busbar cross section: 25 x 3 mm Lugs-ring terminals 1 cable(s) 150 mm ² Connector 1 cable(s) 150 mm ² Power circuit: bolted connection
Tightening torque	18 N.M
Operating time	35...40 ms latching 50...100 ms unlatching
Mechanical durability	1 Mcycles
Maximum operating rate	120 Cyc/H 40 °C

Complementary

Control circuit voltage limits	Latching: 0.85...1.1 Uc Unlatching: 0.85...1.1 Uc
Average coil consumption	1750 VA AC 50...400 Hz latching 11 VA AC 50...400 Hz unlatching 1750 VA DC latching 11 VA DC unlatching

Environment

Protective treatment	TC
Ambient air temperature for operation	-15...70 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without
Height	174 Mm
Width	168.5 Mm
Depth	181 Mm
Net weight	4.6 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------