



### Main

Product or component type	Dimmer
Local signalling	On: indicator light, LED (amber) Off: indicator light, LED (blue)
Additional information	With memory push
[Ue] rated operational voltage	220...240 V AC 50 Hz
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Cover frame colour tint	White

### Complementary

Wiring device mounting	Flush Surface
Clamping connection capacity	2 x 4 mm <sup>2</sup> for solid cable(s) 2 x 4 mm <sup>2</sup> for stranded cable(s) 3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s)
Rated operational power in VA	350 VA
Number of gangs	1 gang
Load type	LV halogen Incandescent lamp
Embedding depth	6 Mm
Width	87 Mm
Height	87 Mm
Depth	35 Mm

### Environment

Maximum ambient air temperature for operation	40 °C
Relative humidity	10...95 %
Ambient air temperature for storage	0...60 °C
Standards	IEC 60669-2-1

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
-------------------	---

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------