



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range of product	TeSys
Device short name	GV2DP
Product or component type	Motor starter
Motor starter type	Reversing
Coordination type	Type 2
Poles description	3P
Utilisation category	AC-3
Motor power kW	4 KW at 440 V AC 50/60 Hz 3 KW at 400/415 V AC 50/60 Hz 4 KW at 400/415 V AC 50/60 Hz 4 KW at 500 V AC 50/60 Hz 5.5 KW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	110 V AC 50/60 Hz
Magnetic tripping current	138 A

Complementary

Device composition	1 3-pole reversing contactor 1 combination block GV2AF3 1 motor circuit breaker type GV2P
Thermal protection adjustment range	6...10 A
Rated breaking capacity	Iq 130 kA at 400/415 V conforming to IEC 60947-4-1 Iq 130 kA at 440 V conforming to IEC 60947-4-1 Iq 50 kA at 500 V conforming to IEC 60947-4-1
Net weight	1.153 Kg
Height	186.8 Mm
Width	90 Mm
Depth	111.9 Mm

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**