



Main

Range of product	PacDrive 3
Product or component type	Servo motor integrated drive
Device short name	ILM

Complementary

[Us] rated supply voltage	250...700 V
Continuous stall current	2.9 A
Continuous stall torque	4.4 N.m
Peak stall torque	18.3 N.m
Nominal output power	910 W
Nominal torque	2.9 N.m
Nominal speed	3000 rpm
Maximum current Irms	13.1 A
[In] rated current	2 A
Shaft end	Untapped
Second shaft	Without second shaft end
Shaft diameter	19 mm
Shaft length	40 mm
Key width	30 mm
Feedback type	Absolute multiturn SinCos Hiperface
Speed feedback resolution	128 periods
Holding brake	Without
Mounting support	International standard flange
Motor flange size	100 mm
Torque constant	1.52 N.m/A at 120 °C
Back emf constant	100 V/krpm at 20 °C
Number of motor poles	8
Rotor inertia	2.31 kg.cm ²
Stator resistance	4.12 Ohm at 20 °C for Ph/Ph 2.86 Ohm at 120 °C for Ph/N
Stator inductance	21.8 mH at 20 °C for Ph/Ph 10.9 mH at 120 °C for Ph/N
Maximum radial force Fr	690 N at 3000 rpm 790 N at 2000 rpm 990 N at 1000 rpm
Maximum axial force Fa	0.2 x Fr

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Type of cooling	Natural convection
Length	249 mm
Number of motor stacks	2
Centring collar diameter	95 mm
Centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	9 mm
Circle diameter of the mounting holes	115 mm
Product weight	6.4 kg

Environment

IP degree of protection	IP54
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1235 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End Of Life Information

Product Life Status : **Commercialised**