



## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	User manual USB cable
Number of tare power	16 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	WS

## Physical

Cable length	1.83 M
Colour	Black
Depth	31 Cm
Height	19 Cm
Mounting preference	No preference
Net weight	6.8 Kg
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No
Width	9.1 Cm

## Input

Network frequency	60 Hz +/- 3 Hz
Plug standard	NEMA 5-15P
Input voltage limits	88...139 V
Maximum input current	12 A
Switching current capacity	15 A
Number of cables	1
Input voltage	120 V

## Output

Rated power in W	510 W
Maximum configurable power in W	510 W
Output frequency	60 Hz sync to mains
UPS type	Line interactive
Wave type	Stepped approximation to a sine wave
Nb of power socket outlets	4 NEMA 5-15R 4 NEMA 5-15R surge
Curve equation	Efficiency
Curve fixed loss	0.0048
Curve load maximum	100 %
Curve load minimum	1 %
Curve proportional loss	0
Curve square loss	0.0043
Curve X-axis maximum	100 %
Curve test cond ID	Curve fit of data measured in accordance with the US DOE Test Procedure for Uninterruptible Power Supplies. All measurements taken in normal mode(s), at typical environmental conditions, with 120V/60Hz electrical input and balanced resistive load (PF = 1.0) output.
Curve X-axis minimum	0 %
Curve X-axis title	Load
Curve X-axis units	Percentage
Curve Y-axis maximum	100 %
Curve Y-axis minimum	50 %
Curve Y-axis title	Efficiency
Curve Y-axis units	Percentage
Graph display	1
Maximum output current	15 A
Output voltage	120 V
Maximum configurable power in VA	850 VA
Rated power in VA	850 VA
Transfer time	8 ms typical : 10 ms maximum

## Conformance

Product certifications	California Energy Commission (CEC) NOM TUV C-US certified
Standards	FCC part 15 class B
Equipment protection policy	Lifetime : \$250000

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...3048.00 M
Acoustic level	45 dBA
Heat dissipation	48.5 Btu/H
Show note OP temperature	No

## Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	1
Number of battery free slots	0
Battery recharge time	12 H
Number of battery replacement quantity	1

Liquid value	0
Battery curve	C
Battery charger power	7 W rated
Battery power in VAH	89 VAh capacity 89 VAh runtime
Battery life	3...5 Year(S)
Extended runtime	0

## Communications & Management

Control panel	Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm

## Surge Protection and Filtering

Surge energy rate	1103 J
Noise suppression	Full time multi-pole noise filtering : 5% of IEEE surge let-through : zero clamping response time: instantaneous
Data line protection	RJ45 10/100/1000 Base-T Ethernet protection Coaxial cable for CATV/SATV/modem/audio-video

## Packing Units

Package 1 Weight	7.6 Kg
Package 1 Height	25.3 Cm
Package 1 width	14.2 Cm
Package 1 Length	44.2 Cm
SCC14	10731304337307
Number of Units in Package 2	2
Package 2 Weight	16.00 Kg
Package 2 Height	279.40 Mm
Package 2 width	304.80 Mm
Package 2 Length	457.20 Mm
Number of Units in Package 3	48
Pallet unit layers	3

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product

## Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**