

Main

Range	TeSys
Product name	TeSys B
Product or component type	Contactor
Device short name	LC1BL
Contactor application	Motor-heating-lighting
Utilisation category	AC-1
Control circuit type	AC
Coil type	Standard
Poles description	4P
Pole contact composition	4 NO
[Ie] rated operational current	800 A (at <40 °C) AC AC-1 for power circuit
Auxiliary contact composition	3 NO + 1 NC
[Uc] control circuit voltage	415 V AC 50...400 Hz

Complementary

Protective cover	With
Auxiliary contacts type	Type instantaneous 3 NO + 1 NC
Control circuit voltage limits	Drop-out: 0.3...0.5 U _c Operational: 0.85...1.1 U _c
[Ui] rated insulation voltage	1000 V - for power circuit conforming to IEC 60158-1 1000 V - for power circuit conforming to IEC 60947-4 1500 V - for power circuit conforming to VDE 0110 group C
Tightening torque	Power circuit: 21 N.m - on bars
[Ue] rated operational voltage	Power circuit: ≤ 1000 V AC 50/60 Hz
[I _{th}] conventional free air thermal current	800 A (at 40 °C) for power circuit
Irms rated making capacity	10000 A at 1000 V AC for power circuit conforming to IEC 60158-1 10000 A at 1000 V AC for power circuit conforming to IEC 60947-4
Rated breaking capacity	10000 A at 440 V for power circuit conforming to IEC 60158-1 10000 A at 440 V for power circuit conforming to IEC 60947-4 4000 A at 1000 V for power circuit conforming to IEC 60158-1 4000 A at 1000 V for power circuit conforming to IEC 60947-4 8000 A at 660...690 V for power circuit conforming to IEC 60158-1 8000 A at 660...690 V for power circuit conforming to IEC 60947-4 9000 A at 500 V for power circuit conforming to IEC 60158-1 9000 A at 500 V for power circuit conforming to IEC 60947-4
Associated fuse rating	1000 A gI at ≤ 440 V for power circuit 800 A aM at ≤ 440 V for power circuit 800 A gI at ≤ 440 V for power circuit
Average impedance	0.18 MOhm - I _{th} 800 A 50 Hz for power circuit
Power dissipation per pole	115 W AC-1 - I _{th} 800 A
Inrush power in VA	1600 VA
Hold-in power consumption in VA	47 VA
Operating time	100...150 ms closing 20...40 ms opening
Mechanical durability	1200000 Cycles
Maximum operating rate	120 Cyc/H 55 °C
Rated operational power in VA	2000 VA at 110...127 V AC-1 - electrical durability: 1000000 cycles - for control circuit 3500 VA at 500 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 220 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 380 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 415...440 V AC-1 - electrical durability: 1000000 cycles - for control circuit
Rated operational power in W	200 W at 500 V AC - electrical durability: 1000000 cycles - for control circuit 230 W at 440 V AC - electrical durability: 1000000 cycles - for control circuit 250 W at 110 V AC - electrical durability: 1000000 cycles - for control circuit 250 W at 220 V AC - electrical durability: 1000000 cycles - for control circuit

Height	486 Mm
Width	475 Mm
Depth	475 Mm
Net weight	72 Kg

Environment

Standards	BS 5424 IEC 60158-1 IEC 60947-4 VDE 0660 NF C 63-110
Product certifications	CSA RINA BV
Protective treatment	TC TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**