



Main

Range	AvatarOn
Product or component type	Switch
Device application	Control
Load type	Incandescent lamp Resistive Inductive Fluorescent lamp
Colour tint	White

Complementary

Rated current	16 A at 250 V AC 50/60 Hz
Switch function	1-way
Number of gangs	2 gangs
Number of rocker	2
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - terminals	Brass terminal
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator
Device mounting	Surface Flush
Width	86 Mm
Height	86 Mm
Depth	34.2 Mm

Environment

Maximum ambient air temperature for operation	45 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	2000 m
Standards	IEC 60669-1 MS IEC 60669-1 SS 227-1 BS EN 60669-1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**