



### Main

Range	EVlink
Product name	EVlink parking
Product or component type	Enclosure
Device short name	EVP2
Range compatibility	EVlink parking EVF2 charging station EVlink parking EVW2 charging station
Poles description	1P + N for control circuit 1P + N for power circuit
Mounting mode	Floor-standing Wall-mounted
Offer type	Standard
[Us] rated supply voltage	230 V AC 50/60 Hz power circuit 220...240 V AC 50/60 Hz control circuit
Earthing system	TT TN IT
Socket number	2
Socket-outlet type	Right side: T2 / silver plated contacts Left side: T2 / silver plated contacts
Maximum supply current	32 A for T2
Nominal output power	7 KW for T2
Access control system	Badge RFID conforming to ISO/IEC 14443 Badge RFID conforming to ISO/IEC 15693

### Complementary

Control type	2 red push-button, function: stop 2 green illuminated push-button, function: start/unlock flap
Local signalling	On charge: 2 LED (green) (flashing) on side Available: 2 LED (green) on front Reserved: 2 LED (orange) on front Not operational: 2 LED (red) on front
Web server	Embedded
Ethernet service	Configuration via web server
Height	625 Mm
Width	400 Mm
Depth	206 Mm
Net weight	20 Kg
Colour	Grey (RAL 7016)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

IP degree of protection	IP54 off load conforming to IEC 61851-1 IP54 on load conforming to IEC 61851-1
IK degree of protection	IK10 charging station conforming to IEC 61851-22 IK10 socket-outlet conforming to IEC 61851-22
Ambient air temperature for operation	-25...50 °C conforming to IEC 61851-22
Ambient air temperature for storage	-40...80 °C
Operating altitude	0...2000 m conforming to IEC 61851-22
Relative humidity	0...95 %

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

Product Life Status : **Commercialised**