



by Schneider Electric



## Main

|                                   |  |
|-----------------------------------|--|
| Range of product                  | OsiSense XM  |
| Pressure sensor type              | Electromechanical pressure sensor  |
| Pressure sensor name              | FYG  |
| Pressure sensor size              | 10.5 bar   |
| Fluid connection type             | G 1/4 (female) conforming to ISO 228   |
| Controlled fluid                  | Fresh water (0...70 °C)<br>Sea water (0...70 °C)   |
| Cable entry                       | 2 entries incorporating Pg 13.5 plastic cable gland, cable outer diameter: 9...13 mm conforming to NF C 68-300 |
| Contacts type and composition     | 2 NC snap action   |
| Product specific application      | -  |
| Pressure switch type of operation | Regulation between 2 thresholds  |
| [In] rated current                | 10 A at 250 V AC conforming to EN 60730-1  |
| Electrical connection             | Screw-clamp terminals, clamping capacity: 1 x 1...2 x 2 mm <sup>2</sup>  |
| Short-circuit protection          | 20 A cartridge fuse type gG  |
| Scale type                        | Adjustable differential  |
| Setting                           | Internal   |
| Local display                     | Without  |
| Electrical circuit type           | Power circuit  |

## Complementary

|   |  |
|---|--|
| Materials in contact with fluid                         | Zinc plated steel<br>Nitrile<br>Nylon 6/6  |
| Enclosure material                                      | PS   |
| Operating position                                      | Any position   |
| Motor power kW  | 0.75 kW/1 hp at 110 V AC, 1 phase<br>1.1 kW/1.5 hp at 110 V AC, 3 phases<br>1.5 kW/2 hp at 230 V AC, 1 phase<br>1.5 kW/2 hp at 400 V AC, 1 phase<br>2.2 kW/3 hp at 230 V AC, 3 phases<br>2.2 kW/3 hp at 400 V AC, 3 phases |
| Adjustable range of switching point on falling pressure | 2.6...8.2 bar  |
| Adjustable range of switching point on rising pressure  | 5.6...10.5 bar   |
| Possible differential minimum at low setting            | 1.9 bar  |

|   |                                    |
|---|------------------------------------|
| Possible differential minimum at high setting   | 2.3 bar                            |
| Possible differential maximum at low setting    | 3 bar                              |
| Possible differential maximum at high setting   | 3.4 bar                            |
| Maximum permissible accidental pressure         | 15 bar                             |
| Maximum permissible pressure - per cycle        | 13 bar                             |
| Destruction pressure                            | 20 bar                             |
| Pressure actuator                               | Diaphragm                          |
| Electrical durability                           | 100000 cycles at 10 cyc/mn         |
| Mechanical durability                           | 1000000 cycles                     |
| Terminal block type                             | 4 terminals                        |
| Possible differential minimum at middle setting | 2.1 bar                            |
| Possible differential maximum at middle setting | 3.2 bar                            |
| Operating rate                                  | 10 cyc/mn                          |
| [Ui] rated insulation voltage                   | 500 V conforming to EN/IEC 60947-1 |
| [Uimp] rated impulse withstand voltage          | 6 kV conforming to EN/IEC 60947-1  |
| Product weight                                  | 0.34 kg                            |
| Repeat accuracy                                 | < 2 %                              |
| Terminals description ISO n°1                   | (1-2)NC<br>(3-4)NC                 |
| Depth   | 106 mm                             |
| Height  | 115 mm                             |
| Width   | 72 mm                              |

## Environment

|                                       |                                 |
|---------------------------------------|---------------------------------|
| Standards                             | CE<br>EN/IEC 60730              |
| Ambient air temperature for operation | 0...45 °C                       |
| Ambient air temperature for storage   | -30...80 °C                     |
| Protective treatment                  | TC                              |
| Electrical shock protection class     | Class I conforming to IEC 536   |
| IP degree of protection               | IP65 conforming to EN/IEC 60529 |


## Offer Sustainability

|                                  |  |
|----------------------------------|--|
| Sustainable offer status         | Green Premium product  |
| RoHS (date code: YYWW)           | Compliant - since 0627 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold  |
| Product environmental profile    | Available <a href="#">Product Environmental Profile</a>  |
| Product end of life instructions | Available <a href="#">End Of Life Information</a>  |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Dimensions




---

Wiring Diagram


---

Connections




Curves

Operating Curves



- (y) Rising pressure
- (x) Falling pressure
- 1 : Maximum differential
- 2 : Minimum differential



- (y) Pressure
- (x) Time
- (1) Adjustable value

|  |
|--|
| Product Life Status : <span style="color: red; font-weight: bold;">Commercialised</span> |
|--|