



Main

Range of product	TeSys
Device short name	GV2DP
Product or component type	Motor starter
Motor starter type	Non reversing
Coordination type	Type 2
Poles description	3P
Utilisation category	AC-3
Motor power kW	0.75 kW at 440 V AC 50/60 Hz 0.75 kW at 400/415 V AC 50/60 Hz 1.1 kW at 440 V AC 50/60 Hz 1.1 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
Magnetic tripping current	33.5 A

Complementary

Device composition	1 combination block GV2AF3 1 motor circuit breaker type GV2P 1 3-pole contactor
Thermal protection adjustment range	1.6...2.5 A
Rated breaking capacity	Iq 130 kA at 400/415 V conforming to IEC 60947-4-1 Iq 130 kA at 440 V conforming to IEC 60947-4-1 Iq 130 kA at 500 V conforming to IEC 60947-4-1
Product weight	0.686 kg
Height	176.4 mm
Width	45 mm
Depth	105.6 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1824 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details- Go to CaP for more details
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------