



Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range	C-Bus
Product or component type	Dimmer
Device application	Control
Load type	Incandescent: 20 W (minimum)
Provided equipment	RCCB, 2
Number of channels	6

Complementary

Maximum leakage current	10 MA leading edge 1 MA trailing edge
[Us] rated supply voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting time	0.5 s
Rated breaking capacity	6 KA
[Ui] rated insulation voltage	500 V

Environment

Dielectric strength	2500 V
Directives	2002/95/EC - RoHS directive 2004/108/EC - electromagnetic compatibility
Standards	EN 61000-3-3 EN 61000-3-2 EN 61000-3-5 EN 55014-1 AS/NZS CISPR 14-1 EN 61000-3-11 IEC 60669-2-1 IEC 60439-1 AS/NZS 3439-1 AS/NZS CISPR 15 EN 55015

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope) [EU RoHS Declaration](#)

Product Life Status : **End of commercialisation**