



Main

Range	TeSys
Product name	TeSys B
Product or component type	Contactor
Device short name	LC1BL
Contactor application	Motor-heating-lighting
Utilisation category	AC-1 AC-3
Control circuit type	AC
Coil type	Standard
Poles description	3P
Pole contact composition	3 NO
[Ie] rated operational current	800 A (at <40 °C) AC AC-1 for power circuit 750 A (at <55 °C) AC AC-3 for power circuit
Motor power kW	220 kW at 220...230 V AC 50/60 Hz 400 kW at 380...400 V AC 50/60 Hz 425 kW at 415 V AC 50/60 Hz 450 kW at 440 V AC 50/60 Hz 500 kW at 500 V AC 50/60 Hz 530 kW at 1000 V AC 50/60 Hz 560 kW at 660...690 V AC 50/60 Hz
Auxiliary contact composition	4 NO
[Uc] control circuit voltage	400 V AC 50...400 Hz

Complementary

Control circuit voltage limits	Drop-out: 0.3...0.5 Uc at 50...400 Hz Operational: 0.85...1.1 Uc at 50...400 Hz
[Ui] rated insulation voltage	1000 V - for power circuit conforming to IEC 60158-1 1000 V - for power circuit conforming to IEC 60947-4 1500 V - for power circuit conforming to VDE 0110 group C
Mounting mode	Fixed
Mounting support	Notched mounting rails Bar support bracket
Tightening torque	Power circuit: 21 N.m - on bars
[Ue] rated operational voltage	Power circuit: ≤ 1000 V AC 50/60 Hz
[Ith] conventional free air thermal current	800 A (at 40 °C) for power circuit
Rms rated making capacity	10000 A at 1000 V AC for power circuit conforming to IEC 60158-1 10000 A at 1000 V AC for power circuit conforming to IEC 60947-4

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Rated breaking capacity	10000 A at 440 V for power circuit conforming to IEC 60158-1 10000 A at 440 V for power circuit conforming to IEC 60947-4 4000 A at 1000 V for power circuit conforming to IEC 60158-1 4000 A at 1000 V for power circuit conforming to IEC 60947-4 8000 A at 660...690 V for power circuit conforming to IEC 60158-1 8000 A at 660...690 V for power circuit conforming to IEC 60947-4 9000 A at 500 V for power circuit conforming to IEC 60158-1 9000 A at 500 V for power circuit conforming to IEC 60947-4
Associated fuse rating	1000 A gI at <= 440 V for power circuit 800 A aM at <= 440 V for power circuit 800 A gI at <= 440 V for power circuit
Average impedance	0.18 MOhm - Ith 800 A 50 Hz for power circuit
Power dissipation per pole	115 W AC-1 - Ith 800 A 88 W AC-3 - Ith 800 A
Inrush power in VA	1300 VA
Hold-in power consumption in VA	31 VA 50/60 Hz
Operating time	100...150 ms closing 50...100 ms opening
Mechanical durability	1200000 Cycles
Maximum operating rate	120 Cyc/H 55 °C
Height	486 Mm
Width	570 Mm
Depth	475 Mm
Net weight	58 Kg

Environment

Standards	IEC 60158-1 BS 5424 VDE 0660 IEC 60947-4 NF C 63-110
Product certifications	BV CSA RINA
Protective treatment	TC TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**