

Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range	TeSys
Product name	TeSys B
Product or component type	Contactor
Device short name	LC1BM
Contactor application	Motor-heating-lighting
Utilisation category	AC-1
Control circuit type	AC
Coil type	Standard
Poles description	4P
Pole contact composition	4 NO
[Ie] rated operational current	1250 A (at <40 °C) AC AC-1 for power circuit
Auxiliary contact composition	4 NO
[Uc] control circuit voltage	220 V AC 50...400 Hz

Complementary

Protective cover	With
Auxiliary contacts type	Type instantaneous 4 NO
Control circuit voltage limits	Drop-out: 0.3...0.5 U _c Operational: 0.85...1.1 U _c
[Ui] rated insulation voltage	1000 V - for power circuit conforming to IEC 60158-1 1000 V - for power circuit conforming to IEC 60947-4 1500 V - for power circuit conforming to VDE 0110 group C
Tightening torque	Power circuit: 35 N.m - on bars
[Ue] rated operational voltage	Power circuit: ≤ 1000 V AC 50/60 Hz
[Ith] conventional free air thermal current	1250 A (at 40 °C) for power circuit
Rms rated making capacity	10000 A at 1000 V AC for power circuit conforming to IEC 60158-1 10000 A at 1000 V AC for power circuit conforming to IEC 60947-4
Rated breaking capacity	10000 A at 440 V for power circuit conforming to IEC 60158-1 10000 A at 440 V for power circuit conforming to IEC 60947-4 4000 A at 1000 V for power circuit conforming to IEC 60158-1 4000 A at 1000 V for power circuit conforming to IEC 60947-4 8000 A at 660...690 V for power circuit conforming to IEC 60158-1 8000 A at 660...690 V for power circuit conforming to IEC 60947-4 9000 A at 500 V for power circuit conforming to IEC 60158-1 9000 A at 500 V for power circuit conforming to IEC 60947-4
Associated fuse rating	1200 A aM at ≤ 440 V for power circuit 1200 A gI at ≤ 440 V for power circuit 1500 A gI at ≤ 440 V for power circuit
Average impedance	0.18 MOhm - Ith 1250 A 50 Hz for power circuit
Power dissipation per pole	280 W AC-1 - Ith 1250 A
Inrush power in VA	1600 VA
Hold-in power consumption in VA	47 VA
Operating time	100...150 ms closing 20...40 ms opening
Mechanical durability	1200000 Cycles
Maximum operating rate	120 Cyc/H 55 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Rated operational power in VA	2000 VA at 110...127 V AC-1 - electrical durability: 1000000 cycles - for control-circuit 3500 VA at 500 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 220 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 380 V AC-1 - electrical durability: 1000000 cycles - for control circuit 4000 VA at 415...440 V AC-1 - electrical durability: 1000000 cycles - for control-circuit
Rated operational power in W	200 W at 500 V AC - electrical durability: 1000000 cycles - for control circuit 230 W at 440 V AC - electrical durability: 1000000 cycles - for control circuit 250 W at 110 V AC - electrical durability: 1000000 cycles - for control circuit 250 W at 220 V AC - electrical durability: 1000000 cycles - for control circuit
Height	500 Mm
Width	475 Mm
Depth	790 Mm
Net weight	71 Kg

Environment

Standards	VDE 0660 BS 5424 IEC 60947-4 NF C 63-110 IEC 60158-1
Product certifications	RINA CSA BV
Protective treatment	TC TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	3000 m without

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**