



Main

Range	Masterpact
Device short name	MN diag
Product or component type	Voltage release
Device application	Safety
Range compatibility	Masterpact MTZ1 circuit breaker Masterpact MTZ2 circuit breaker Masterpact MTZ3 circuit breaker
Voltage release type	Undervoltage release

Complementary

Control type	Communicating
Signalling function	MN open Coil powered Error
[Uc] control circuit voltage	200...250 V AC 50/60 Hz 200...250 V DC
Threshold tripping voltage	0.35...0.7 Un opening 0.85 Un closing
Supply holding power	4.5 VA
Mounting mode	Fixed
Response time	40 ms +/- 5 % for Masterpact MTZ1 90 ms +/- 5 % for Masterpact MTZ2 90 ms +/- 5 % for Masterpact MTZ3
Offer type	Spare part

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental Disclosure

 [Product Environmental Profile](#)

Circularity Profile

 [End Of Life Information](#)

Product Life Status : **Commercialised**